



### TECHNICAL INFORMATION

Watts:	15
Lumens:	1500
Shape:	Round
Input Power:	AC:220-240V, 50/60Hz
Long Life:	20,000 Hours
Unit Color:	White
Body Type:	PC
PF:	>0.6
LED Chip Type:	SMD-Samsung Chip
CRI:	>80
Beam Angle:	110°
Color Temperature:	6500K
Dimension:	200x47.5mm
lumens per watt:	100

### PRO TRIMLESS DOME LIGHTS | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

*One brand. endless solutions..*

SKU: 13899 - 1281 940

[View more details](#)



### FEATURES

- Uses High Quality Power Driver and LED Chip
- Excellent heat dissipation
- Robust PC body for utility applications
- IP44 ingress protection
- Excellent heat dissipation
- Applications - Living Room, Bedroom, Utilities, Passage etc

### PACKAGING

Gross Weight (Kgs): 0.52  
Unit CBM: 0.002886  
Dimension: 200x47.5mm

### MASTER BOX PACKAGING

Box Qty: 20  
Qty Per Pallet: 400  
Length (Box) mm: 215  
Width (Box) mm: 205  
Height (Box) mm: 55

### LISTING DETAILS

Commodity Code: 9405104090  
Ean Code: 3800157657532