



TECHNICAL INFORMATION

Watts:	25
Lumens:	2500
Shape:	Round
Input Power:	AC:220-240V, 50/60Hz
Long Life:	20,000 Hours
Unit Color:	White
Body Type:	PC
PF:	>0.9
LED Chip Type:	SMD-Samsung Chip
CRI:	>80
Beam Angle:	110°
Color Temperature:	4000K
Dimension:	300x50mm
lumens per watt:	100

PRO TRIMLESS DOME LIGHTS | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

One brand. endless solutions..

SKU: 13939 - 1560 940

[View more details](#)



FEATURES

- Uses High Quality Power Driver and LED Chip
- Excellent heat dissipation
- Robust PC body for utility applications
- IP44 ingress protection
- Excellent heat dissipation
- Applications - Living Room, Bedroom, Utilities, Passage etc

PACKAGING

Gross Weight (Kgs): 1.01
Unit CBM: 0.006229
Dimension: 300x50mm

MASTER BOX PACKAGING

Box Qty: 10
Qty Per Pallet: 200
Length (Box) mm: 315
Width (Box) mm: 305
Height (Box) mm: 55

LISTING DETAILS

Commodity Code: 9405104090
Ean Code: 3800157657587