



### TECHNICAL INFORMATION

Watts:	25
Lumens:	2500
Shape:	Square
Input Power:	AC:220-240V, 50/60Hz
Long Life:	20,000 Hours
Unit Color:	White
Body Type:	PC
PF:	>0.9
LED Chip Type:	SMD-Samsung Chip
CRI:	>80
Beam Angle:	110°
Color Temperature:	4000K
Dimension:	300x300x50mm
lumens per watt:	100

### PRO TRIMLESS DOME LIGHTS | LED LIGHTING


<p>V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.</p>

*One brand, endless solutions..*

SKU: 13969 - 1560 940

[View more details](#)

### SMD LED'S



### FEATURES

- Uses High Quality Power Driver and LED Chip
- Excellent heat dissipation
- Robust PC body for utility applications
- IP44 ingress protection
- Excellent heat dissipation
- Applications - Living Room, Bedroom, Utilities, Passage etc

### PACKAGING

Gross Weight (Kgs):	1.2
Unit CBM:	0.006231
Dimension:	300x300x50mm

### MASTER BOX PACKAGING

Box Qty:	10
Qty Per Pallet:	200
Length (Box) mm:	315
Width (Box) mm:	305
Height (Box) mm:	55

### LISTING DETAILS

Commodity Code:	9405104090
Ean Code:	3800157657556