



LIGHT SENSOR PRO | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

One brand. endless solutions..

SKU: 20175 - 934 938

[View more details](#)

TECHNICAL INFORMATION

| | |
|------------------------|-------------------|
| Watts: | 100 |
| Lumens: | 10000 |
| Input Power: | AC:220-240V, 50Hz |
| Long Life: | 25,000 Hours |
| Unit Color: | Black |
| Body Type: | Diecast Aluminium |
| PF: | >0.9 |
| LED Chip Type: | SMD-Samsung Chip |
| CRI: | >80 |
| Operation Temperature: | -20°C to +45°C |
| Dimmable: | No |
| Beam Angle: | 100° |
| Color Temperature: | 3000K |
| Dimension: | 247.5x49.5x299mm |
| Sensor Type: | Light Sensor |
| lumens per watt: | 100 |



SMD LED'S

5 YEAR WARRANTY



IP65
RATING



5 YEAR
WARRANTY



IK 05



CRI > 80



100
Lumen/W



SAVE UP TO
85%
ENERGY

FEATURES

- High quality Light Sensor Floodlight with a lumen output of 100LM/W
- Designed with high efficiency LED Samsung Chips
- Light Sensor function with no turning on/off required
- When natural light is above 140Lux floodlight will be auto off and below 140Lux will be auto on
- Light Sensor Floodlight donot detect any motion
- Built Strong and durable with Die Cast Aluminium - Corrosion resistant design
- Perfectly built for outdoor with Ingress protection of IP65
- Application - Facade lighting, lobby, garage, passage, parking lot and many more



PACKAGING

Gross Weight (Kgs): 1.72
Unit CBM: 0.00545
Dimension: 247.5x49.5x299mm

MASTER BOX PACKAGING

Box Qty: 4
Length (Box) mm: 252
Width (Box) mm: 54
Height (Box) mm: 304

LISTING DETAILS

Ean Code: 3800157660433