



LIGHT SENSOR PRO | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 20176 - 934 938

[View more details](#)

TECHNICAL INFORMATION

Watts:	100
Lumens:	10000
Input Power:	AC:220-240V, 50Hz
Long Life:	25,000 Hours
Unit Color:	Black
Body Type:	Diecast Aluminium
PF:	>0.9
LED Chip Type:	SMD-Samsung Chip
CRI:	>80
Operation Temperature:	-20°C to +45°C
Dimmable:	No
Beam Angle:	100°
Color Temperature:	4000K
Dimension:	247.5x49.5x299mm
Sensor Type:	Light Sensor
lumens per watt:	100



SMD LED'S

5 YEAR WARRANTY



IP65
RATING



5 YEAR
WARRANTY



IK 05



CRI > 80



100
Lumen/W



SAVE UP TO
85%
ENERGY

FEATURES

- High quality Light Sensor Floodlight with a lumen output of 100LM/W
- Designed with high efficiency LED Samsung Chips
- Light Sensor function with no turning on/off required
- When natural light is above 140Lux floodlight will be auto off and below 140Lux will be auto on
- Light Sensor Floodlight donot detect any motion
- Built Strong and durable with Die Cast Aluminium - Corrosion resistant design
- Perfectly built for outdoor with Ingress protection of IP65
- Application - Facade lighting, lobby, garage, passage, parking lot and many more



PACKAGING

Gross Weight (Kgs): 1.72
Unit CBM: 0.005442
Dimension: 247.5x49.5x299mm

MASTER BOX PACKAGING

Box Qty: 4
Length (Box) mm: 252
Width (Box) mm: 54
Height (Box) mm: 304

LISTING DETAILS

Ean Code: 3800157660440