



### TECHNICAL INFORMATION

Watts:	50
Lumens:	4000
Input Power:	AC:220-240V, 50Hz
Long Life:	25,000 Hours
Unit Color:	White
Body Type:	Diecast Aluminium
PF:	>0.9
LED Chip Type:	SMD-Samsung Chip
CRI:	>80
Operation Temperature:	-20°C to +40°C
Dimmable:	No
Beam Angle:	100°
Color Temperature:	3000K
Dimension:	195x60x178mm
Sensor Type:	PIR
Detection Distance:	3-10m (Radius)

### PIR SENSOR PRO

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

*One brand, endless solutions..*

SKU: 20301 - 933 940

[View more details](#)



IP65  
RATING



5 YEAR  
WARRANTY



CRI>80



SAVE UP TO  
85%  
ENERGY

### FEATURES

- High quality Slim series PIR Sensor Foodlight with 1 Meter cable
- Designed with high efficiency LED Samsung Chips
- Detects motion within a radius of 3 to 10 Meter
- Installing Height 1.8 Meter to 2.5 Meter
- Built Strong and durable with Die Cast Aluminium - Corrosion resistant design
- Perfectly built for outdoor with Ingress protection of IP65
- Application - Facade lighting, lobby, garage, passage, parking lot and many more



### PACKAGING

Gross Weight (Kgs): 0.86  
Unit CBM: 0.003  
Dimension: 195x60x178mm

### MASTER BOX PACKAGING

Box Qty: 10  
Length (Box) mm: 200  
Width (Box) mm: 63  
Height (Box) mm: 185

### LISTING DETAILS

Ean Code: 3800157661591