



Integral "spring" holds wire bundles tightly. Used in pre-drilled .250" (6.4mm) diameter holes in panels up to .105" (2.7mm) thick. Vertical and horizontal versions available.

Part Number: HCMP06B12-C20  
Product Family: Harness Clips  
Product Line: Push/Tree Barb

RoHS Compliancy Status: Compliant

Part Description: Winged Push Barb Harness Clip

Product Type: Mounting Device

Material: Nylon 6.6

Color: Black

Height (In.): 1.25

Height (mm): 31.8

Length (In.): .74

Length (mm): 10.0

Width (In.):	.59
Width (mm):	15.0
Environment:	Indoor
Max. Bundle Dia. Range (mm):	5.9 – 12.5
Max. Bundle Diameter Range (In.):	.24 – .47
Max. Panel Thickness (In.):	.118
Max. Panel Thickness (mm):	3.0
Mounting Method:	Push Mount
Panel Hole Diameter (In.):	.25
Panel Hole Diameter (mm):	6.4
Std. Pkg. UOM:	PK
UOM:	PC
Std. Pkg. Qty.:	100
Min. Order Qty.:	100