



CorePro LEDspot PAR

CorePro LEDspot ND 9-60W 827 PAR38 25D

CorePro LEDspot PAR are a perfect fit for spot lighting and deliver warm halogen-like light. They are compatible with most existing fixtures with a E27 base and are designed as a retrofit replacement for halogen spots. CorePro LEDspot PAR deliver significant energy savings of up to 80% compared to traditional halogen lamps and provides comfortable lighting for your eyes. By offering a lifetime of 15,000 hours, it lowers maintenance costs.

Product data

General Information		Power (Rated) (Nom)	
Cap base	E27 [E27]		9 W
EU RoHS compliant	Yes	Lamp current (nom.)	44 mA
Nominal lifetime (nom.)	15000 h	Wattage equivalent	60 W
Switching cycle	25,000X	Starting time (nom.)	0.5 s
		Warm-up time to 60% light (nom.)	0.5 s
		Power factor (nom.)	0.9
		Voltage (Nom)	220-240 V
Light Technical		Temperature	
Colour Code	827 [CCT of 2,700 K]	T-Case maximum (nom.)	80 °C
Beam Angle (Nom)	25 °		
Luminous flux (nom.)	750 lm	Controls and Dimming	
Luminous intensity (nom.)	1800 cd	Dimmable	No
Colour designation	Warm white (WW)	Mechanical and Housing	
Correlated Colour Temperature (Nom)	2700 K	Bulb shape	PAR38 [PAR 4.75 inch/121mm]
Luminous efficacy (rated) (nom.)	83.00 lm/W	Approval and Application	
Colour consistency	<6	Energy Efficiency Class	F
Colour rendering index (nom.)	80	Suitable for accent lighting	Yes
LLMF at end of nominal lifetime (nom.)	70 %	Energy consumption kWh/1,000 hours	9 kWh
Luminous flux in 90° cone (rated)	750 lm		
Operating and Electrical			
Input frequency	50 Hz		

CorePro LEDspot PAR


465201

Product Data

Full product code	871951438873400
Order product name	CorePro LEDspot ND 9-60W 827 PAR38 25D
EAN/UPC – product	8719514388734
Order code	38873400

SAP numerator – quantity per pack	1
Numerator – packs per outer box	6
SAP material	929001322732
SAP net weight (piece)	0.385 kg

Dimensional drawing




PAR38 220-240V 11-60W 2700K E27 D


Product

CorePro LEDspot ND 9-60W 827 PAR38 25D


Photometric data



LEDspots Corepro 9W PAR38 E27 827 25D-POC



LEDspots Corepro 9W PAR38 E27 827 25D-LDD




Page 11

LEDspots Corepro 9W PAR38 E27 827 25D-ADL

CorePro LEDspot PAR

Lifetime



15K LED

15K LMP

