



# CorePro LEDcapsule MV

## CorePro LEDcapsuleMV 2.6-25W G9 827 D UK

This single-ended mains-voltage capsule for G9-base luminaires delivers directional light, making it a true alternative to halogen capsule lamps. It is particularly suitable for task lighting in shops, hotels and restaurants, and ideal for desk lamps and cabinet lighting. Compatible with existing fixtures with G9 holders and designed for retrofit replacement of halogen capsules, CorePro LEDcapsule delivers huge energy savings and minimizes maintenance costs, without any compromise on light quality.

### Product data

General Information		Lamp current (nom.)	
Cap base	G9 [ G9]		14.5 mA
EU RoHS compliant	Yes	Wattage equivalent	25 W
Nominal lifetime (nom.)	15000 h	Starting time (nom.)	0.5 s
Switching cycle	50,000X	Warm-up time to 60% light (nom.)	0.5 s
		Power factor (nom.)	0.7
		Voltage (Nom)	220-240 V
Light Technical		Temperature	
Colour Code	827 [ CCT of 2,700 K]	T-Case maximum (nom.)	86 °C
Luminous flux (nom.)	300 lm		
Colour designation	Warm white (WW)	Controls and Dimming	
Correlated Colour Temperature (Nom)	2700 K	Dimmable	Yes
Luminous efficacy (rated) (nom.)	115.00 lm/W		
Colour consistency	<6	Mechanical and Housing	
Colour rendering index (nom.)	80	Bulb shape	Capsule
LLMF at end of nominal lifetime (nom.)	70 %		
Operating and Electrical		Approval and Application	
Input frequency	50 to 60 Hz	Energy Efficiency Class	E
Power (Rated) (Nom)	2.6 W	Suitable for accent lighting	No

# CorePro LEDcapsule MV


Energy consumption kWh/1,000 hours	3 kWh
	374868

## Product Data

Full product code	871869976669601
Order product name	CorePro LEDcapsuleMV 2.6-25W G9 827 D UK
EAN/UPC – product	8718699766696

Order code	76669601
SAP numerator – quantity per pack	1
Numerator – packs per outer box	12
SAP material	929002389999
SAP net weight (piece)	0.012 kg


## Dimensional drawing




Capsule G9 25W 215lm 2700K G9 Dim 15khrs

Product	D	C
CorePro LEDcapsuleMV 2.6-25W G9 827 D UK	15 mm	52 mm


## Photometric data



LEDcapsule MV 2,6W G9 827



LEDcapsule MV 2,6W G9 827




LEDcapsule MV 2,6W G9

# CorePro LEDcapsule MV

## Lifetime



15K LED



15K LMP

