



MASTER Glass LED bulbs

MAS LEDBulb DT5.9-60W E27 927 A60 FR G

Featuring a classic heritage design, Classic filament LED Lamps combine the familiar shapes of incandescent bulbs with the benefits of the long-lasting LED technology. It is an idea product to provide customers with cozy atmosphere. The MASTER LED bulbs can be dimmed for different lumen level and also for the different color temperature. MASTER Glass Led Bulbs deliver significant energy savings, offering even 30% more compared to normal LED and provides excellent quality of light. By offering a lifetime of 25,000 hours it reduces maintenance costs.

Product data


General Information		Operating and Electrical	
Cap-Base	E27 [E27]	Input Frequency	50 to 60 Hz
EU RoHS compliant	Yes	Power (Nom)	5.9 W
Nominal Lifetime (Nom)	25000 h	Lamp Current (Nom)	40 mA
Switching Cycle	20000X	Wattage Equivalent	60 W
Flux measurement reference	Sphere	Starting Time (Nom)	0.5 s
		Warm Up Time to 60% Light (Nom)	0.5 s
		Power Factor (Nom)	0.6
		Voltage (Nom)	220-240 V
Light Technical		Temperature	
Color Code	922-927 [CCT of 2200K-2700K]	T-Case Maximum (Nom)	70 °C
Luminous Flux (Nom)	806 lm		
Color Designation	Warm Glow(WG)	Controls and Dimming	
Correlated Color Temperature (Nom)	2200 2700 K	Dimmable	Only with specific dimmers
Luminous Efficacy (rated) (Nom)	136.00 lm/W		
Color Consistency	<6	Mechanical and Housing	
Color Rendering Index (Nom)	90	Bulb Finish	Frosted
LLMF At End Of Nominal Lifetime (Nom)	70 %		

MASTER Glass LED bulbs

Bulb Shape	A60 [A 60mm]
Approval and Application	
Energy Efficiency Class	D
Energy Consumption kWh/1000 h	6 kWh
EPREL Registration Number	453247
Product Data	
Full product code	871951432475600

Order product name	MAS LEDBulb DT5.9-60W E27 927 A60 FR G
EAN/UPC - Product	8719514324756
Order code	929003010402
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929003010402
Net Weight (Piece)	0.030 kg


Dimensional drawing




Bulb A60 EU 6-60W 810lm WG E27 FR

Product	D	C
MAS LEDBulb DT5.9-60W E27 927 A60 FR G	60 mm	104 mm

Photometric data




LEDbulb MAS SLR 5,9W A60 E27 927 CL-POC



LEDbulb MAS SLR 5,9W A60 E27 927 FR-GUL

MASTER Glass LED bulbs

Photometric data



LEDbulb MAS SLR A60 5,9W E27 927 FR-LDD

Lifetime



LEDspots LED 25K



LEDspots LMP 25K

