



MASTER Glass LED bulbs

MAS LEDBulb DT10.5-100W E27 927A60 FR G

Featuring a classic heritage design, Classic filament LED Lamps combine the familiar shapes of incandescent bulbs with the benefits of the long-lasting LED technology. It is an idea product to provide customers with cozy atmosphere. The MASTER LED bulbs can be dimmed for different lumen level and also for the different color temperature. MASTER Glass Led Bulbs deliver significant energy savings, offering even 30% more compared to normal LED and provides excellent quality of light. By offering a lifetime of 25,000 hours it reduces maintenance costs.

Product data


General Information		Operating and Electrical	
Cap-Base	E27 [E27]	Input Frequency	50 to 60 Hz
EU RoHS compliant	Yes	Power (Nom)	10.5 W
Nominal Lifetime (Nom)	25000 h	Lamp Current (Nom)	55 mA
Switching Cycle	20000X	Wattage Equivalent	100 W
Flux measurement reference	Sphere	Starting Time (Nom)	0.5 s
		Warm Up Time to 60% Light (Nom)	0.5 s
		Power Factor (Nom)	0.9
		Voltage (Nom)	220-240 V
Light Technical		Temperature	
Color Code	922-927 [CCT of 2200K-2700K]	T-Case Maximum (Nom)	70 °C
Luminous Flux (Nom)	1521 lm		
Color Designation	Warm Glow(WG)	Controls and Dimming	
Correlated Color Temperature (Nom)	2200 2700 K	Dimmable	Only with specific dimmers
Luminous Efficacy (rated) (Nom)	144.00 lm/W		
Color Consistency	<6	Mechanical and Housing	
Color Rendering Index (Nom)	90	Bulb Finish	Frosted
LLMF At End Of Nominal Lifetime (Nom)	70 %		

MASTER Glass LED bulbs

Bulb Shape	A60 [A 60mm]
Approval and Application	
Energy Efficiency Class	D
Energy Consumption kWh/1000 h	11 kWh
EPREL Registration Number	453260
Product Data	
Full product code	871951432501200

Order product name	MAS LEDBulb DT10.5-100W E27 927A60 FR G
EAN/UPC - Product	8719514325012
Order code	929003011702
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929003011702
Net Weight (Piece)	0.030 kg


Dimensional drawing




Bulb A60 EU 11.5-100W 1560lm WG E27 FR

Product	D	C
MAS LEDBulb DT10.5-100W E27 927A60 FR G	60 mm	108 mm

Photometric data




LEDbulb MAS SLR 10,5W A60 E27 927 CL-POC



LEDbulb MAS SLR A60 10,5W E27 927 FR-LDD

MASTER Glass LED bulbs


Photometric data




© Philips Lighting B.V. 2021

LEDbulb MAS SLR 10,5W A60 E27 927 FR-GUL

Lifetime



LEDspots LED 25K



LEDspots LMP 25K

