



MASTER Value Glass LED bulbs

MASTER VLE LEDBulbD 3.4-40W B22 A60 927FR G

Featuring a classic heritage design, Classic filament LED Lamps combine the familiar shapes of incandescent bulbs with the benefits of the long-lasting LED technology. The product offers more energy saving comparing with normal LED bulbs, while in the same time it also provide the custome with good light experience with super dimming performance. MASTER Value Glass Led Bulbs deliver significant energy savings, offering even 30% more compared to normal LED and provides excellent quality of light. By offering a lifetime of 15,000 hours it reduces maintenance costs.

Product data

General Information	
Cap-Base	B22 [B22]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	15000 h
Switching Cycle	20000X
Flux measurement reference	Sphere
Light Technical	
Color Code	927 [CCT of 2700K]
Luminous Flux (Nom)	470 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	138.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	90

LLMF At End Of Nominal Lifetime (Nom) 70 %	
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Nom)	3.4 W
Lamp Current (Nom)	24 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.6
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	70 °C

MASTER Value Glass LED bulbs

Controls and Dimming

Dimmable	Only with specific dimmers
----------	----------------------------

Mechanical and Housing

Bulb Finish	Frosted
Bulb Shape	A60 [A 60mm]


Approval and Application

Energy Efficiency Class	D
Energy Consumption kWh/1000 h	4 kWh
EPREL Registration Number	453245

Product Data

Full product code	871951432471800
Order product name	MASTER VLE LEDBulbD 3.4-40W B22 A60 927FR G
EAN/UPC - Product	8719514324718
Order code	929003010202
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929003010202
Net Weight (Piece)	0.030 kg


Dimensional drawing




Bulb A60 EU 3.5-40W 475lm WG B22 FR

Product	D	C
MASTER VLE LEDBulbD 3.4-40W B22 A60 927FR G	60 mm	103 mm

Photometric data




LEDbulb MAS SLR A60 3,4W E27 927 FR-LDD



LEDbulb MAS SLR 3,4W A60 B22 927 FR-GUL


MASTER Value Glass LED bulbs

Photometric data




LEDbulb MAS SLR 3,4W A60 E27 927 CL-POC

Lifetime



15K LED



15K LMP

