



CorePro LEDbulb



CorePro LEDbulb ND 10.5-75W A60 E27 930

LEDbulbs are compatible with existing fixtures with an E27 holder and are designed for retrofit replacement of incandescent bulbs.

Product data


General Information	
Cap base	E27 [E27]
EU RoHS compliant	Yes
Nominal lifetime (nom.)	15000 h
Switching cycle	50,000X
	Sphere
Light Technical	
Colour Code	930 [CCT of 3,000 K]
Beam Angle (Nom)	200 °
Luminous flux (nom.)	1055 lm
Colour designation	White (WH)
Correlated Colour Temperature (Nom)	3000 K
Luminous efficacy (rated) (nom.)	100.00 lm/W
Colour consistency	<6
Colour rendering index (nom.)	90
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	10.5 W
Lamp current (nom.)	83 mA
Wattage equivalent	75 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s

Power factor (nom.)	0.5
Voltage (Nom)	220-240 V
Temperature	
T-Case maximum (nom.)	88 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Lamp Finish	Frosted
Bulb shape	A60 [A 60mm]
Approval and Application	
Energy Efficiency Class	F
Energy consumption kWh/1,000 hours	11 kWh
	438123
Product Data	
Full product code	871951432964500
Order product name	CorePro LEDbulb ND 10.5-75W A60 E27 930
EAN/UPC – product	8719514329645
Order code	32964500
SAP numerator – quantity per pack	1
Numerator – packs per outer box	10

CorePro LEDbulb

SAP material	929003003102
SAP net weight (piece)	0.076 kg



Dimensional drawing



Bulb 220-240V 10.5-W 1055lm 3000K E27 ND

Product	D	C
CorePro LEDbulb ND 10.5-75W A60 E27 930	60 mm	110 mm


Photometric data



General Uniform Lightness

LEDbulb CorePro 10,5W A60 E27 930 FR-POC

LEDbulb CorePro 10,5W A60 E27 930-GUL



LEDbulb CorePro A60 10,5W E27 930 FR-LDD

CorePro LEDbulb

Lifetime



15K LED

15K LMP

