



CorePro LEDbulb

CoreProLEDbulb ND 13-100W A60 E27 930 UK

LEDbulbs are compatible with existing fixtures with an E27 holder and are designed for retrofit replacement of incandescent bulbs.


Product data

General Information		Voltage (Nom)	
Cap base	E27 [E27]	220-240 V	
EU RoHS compliant	Yes	Temperature	
Nominal lifetime (nom.)	15000 h	T-Case maximum (nom.)	95 °C
Switching cycle	50,000X	Controls and Dimming	
Light Technical		Dimmable	No
Colour Code	930 [CCT of 3,000 K]	Mechanical and Housing	
Beam Angle (Nom)	200 °	Lamp Finish	Frosted
Luminous flux (nom.)	1521 lm	Bulb shape	A60 [A 60mm]
Colour designation	White (WH)	Approval and Application	
Correlated Colour Temperature (Nom)	3000 K	Energy Efficiency Class	E
Luminous efficacy (rated) (nom.)	117.00 lm/W	Energy consumption kWh/1,000 hours	13 kWh
Colour consistency	<6		438126
Colour rendering index (nom.)	90	Product Data	
LLMF at end of nominal lifetime (nom.)	70 %	Full product code	871951432968301
Operating and Electrical		Order product name	CoreProLEDbulb ND 13-100W A60 E27 930 UK
Input frequency	50 to 60 Hz	EAN/UPC – product	8719514329683
Power (Rated) (Nom)	13 W	Order code	32968301
Lamp current (nom.)	105 mA	SAP numerator – quantity per pack	1
Wattage equivalent	100 W	Numerator – packs per outer box	10
Starting time (nom.)	0.5 s	SAP material	929003003999
Warm-up time to 60% light (nom.)	0.5 s		
Power factor (nom.)	0.5		

CorePro LEDbulb

SAP net weight (piece) 0.076 kg



Dimensional drawing



Bulb 220-240V 13-W 1521lm 3000K E27 ND


Product	D	C
CoreProLEDbulb ND 13-100W A60 E27 930 UK	60 mm	110 mm

Photometric data



LEDbulb CorePro 13W A60 E27 930-GUL



LEDbulb CorePro 7,5W A60 E27 930 FR-POC



LEDbulb CorePro A60 13W E27 930 FR-LDD

CorePro LEDbulb

Lifetime



15K LED

15K LMP

