



# CorePro LEDbulb



## CorePro LEDbulb ND 10-75W A60 E27 940

LEDbulbs are compatible with existing fixtures with an E27 holder and are designed for retrofit replacement of incandescent bulbs.

### Product data


General Information	
Cap base	E27 [ E27]
EU RoHS compliant	Yes
Nominal lifetime (nom.)	15000 h
Switching cycle	50,000X
	Sphere
Light Technical	
Colour Code	940 [ CCT of 4,000 K]
Beam Angle (Nom)	200 °
Luminous flux (nom.)	1055 lm
Colour designation	Cool White (CW)
Correlated Colour Temperature (Nom)	4000 K
Luminous efficacy (rated) (nom.)	105.00 lm/W
Colour consistency	<6
Colour rendering index (nom.)	90
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	10 W
Lamp current (nom.)	83 mA
Wattage equivalent	75 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s

Power factor (nom.)	0.5
Voltage (Nom)	220-240 V
Temperature	
T-Case maximum (nom.)	88 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Lamp Finish	Frosted
Bulb shape	A60 [ A 60mm]
Approval and Application	
Energy Efficiency Class	F
Energy consumption kWh/1,000 hours	10 kWh
	438125
Product Data	
Full product code	871951432966900
Order product name	CorePro LEDbulb ND 10-75W A60 E27 940
EAN/UPC – product	8719514329669
Order code	32966900
SAP numerator – quantity per pack	1
Numerator – packs per outer box	10

# CorePro LEDbulb

SAP material	929003003302
SAP net weight (piece)	0.076 kg



## Dimensional drawing



Bulb 220-240V 10-W 1055lm 4000K E27 ND

Product	D	C
CorePro LEDbulb ND 10-75W A60 E27 940	60 mm	110 mm


## Photometric data



General Uniform Lightness

LEDbulb CorePro 10W A60 E27 940 FR-POC

LEDbulb CorePro 10W A60 E27 940-GUL



LEDbulb CorePro A60 10,5W E27 930 FR-LDD

# CorePro LEDbulb

## Lifetime



15K LED

15K LMP

