



CorePro Glass LED bulbs



CorePro LEDBulbND 4-40W E27 ST64 827 CLG

Featuring a classic heritage design, Classic filament LED Lamps combine the familiar shapes of classic incandescent bulbs with the benefits of the long-lasting LED technology. An very easy choice for people who are looking for the replacement for retrofit LED bulbs, as comparing with convential lamps, it provide 90% energy saving. CorePro Glass LED bulbs provides excellent quality of light. By offering a lifetime of 15,000 hours it reduces maintenance costs.

Product data

General Information	
Cap-Base	E27 [E27]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	15000 h
Switching Cycle	20000X
Technical Type	4-40W
Flux measurement reference	Sphere
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux (Nom)	470 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	117.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %


Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Nom)	4 W
Lamp Current (Nom)	33 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.4
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	50 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear

CorePro Glass LED bulbs

Bulb Shape	ST64
Approval and Application	
Energy Efficiency Class	E
Energy Saving Product	Yes
Suitable For Accent Lighting	No
Energy Consumption kWh/1000 h	4 kWh
EPREL Registration Number	574354
Product Data	
Full product code	871951434687100

Order product name	CorePro LEDBulbND 4-40W E27 ST64 827 CLG
EAN/UPC - Product	8719514346871
Order code	929001237392
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001237392
Net Weight (Piece)	0.048 kg


Dimensional drawing




filament 4.5W-40W 470lm NAD 2700K E27ND

Product	D	C
CorePro LEDBulbND 4-40W E27 ST64 827 CLG	64 mm	140 mm

Photometric data




LED Lamps, Lightcolour /827 ND CL



CorePro LEDbulb ND 4-40W ST64 827

CorePro Glass LED bulbs

Photometric data



CorePro LEDbulb ND 4-40W ST64 827

Lifetime



15K LED



15K LMP

