

MASTER Value GLASS LED candles and lustres



MASTER VLE LEDCandleDT3.4-40W E27 927B35CLG

Featuring a classic heritage design, Classic filament LED Lamps combine the familiar shapes of incandescent candles and lustres with the benefits of the long-lasting LED technology. The product offers more energy saving compared with normal LED candles and lustres, and also provides the customer with a good light experience and superior dimming performance. MASTER Value Glass Led candles and lustres deliver significant energy savings, offering 30% more compared to normal LEDs. They provide excellent quality of light. By offering a lifetime of 15,000 hours, they reduce maintenance costs.

Product data

General Information	
Cap base	E27 [E27]
EU RoHS compliant	Yes
Nominal lifetime (nom.)	15000 h
Switching cycle	20,000X
	Sphere
Light Technical	
Colour Code	922-927 [CCT of 2,200 K-2,700 K]
Luminous flux (nom.)	470 lm
Colour designation	Warm Glow (WG)
Correlated Colour Temperature (Nom)	2200 2700 K
Luminous efficacy (rated) (nom.)	138.00 lm/W


Colour consistency	<6
Colour rendering index (nom.)	90
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	3.4 W
Lamp current (nom.)	24 mA
Wattage equivalent	40 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.6

MASTER Value GLASS LED candles and lustres

Voltage (Nom)	220-240 V
Temperature	
T-Case maximum (nom.)	70 °C
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Lamp Finish	Clear
Bulb shape	B35 [B 35mm]
Approval and Application	
Energy Efficiency Class	D
Energy consumption kWh/1,000 hours	4 kWh

	453266
Product Data	
Full product code	871951432513500
Order product name	MASTER VLE LEDCandleDT3.4-40W E27 927B35CLG
EAN/UPC – product	8719514325135
Order code	32513500
SAP numerator – quantity per pack	1
Numerator – packs per outer box	10
SAP material	929003012302
SAP net weight (piece)	0.014 kg



Dimensional drawing



Candle B35 EU 3.5-40W 475lm WG E27 CL

Product	D	C
MASTER VLE LEDCandleDT3.4-40W E27 927B35CLG	35 mm	95 mm

Photometric data




LEDcandle MAS SLR 3,4W B35 E27 927 CL-GUL

LEDcandle MAS SLR B35 3,4W E14 927 CL-LDD


MASTER Value GLASS LED candles and lustres

Photometric data




LEDcandle MAS SLR 3,4W B35 E14 927 CL-POC

Lifetime



15K LED



15K LMP

