

MASTER Value GLASS LED candles and lusters

MASTER VLE LEDCandleDT3.4-40W E14927BA35CLG

Featuring a classic heritage design, Classic filament LED Lamps combine the familiar shapes of incandescent candles and lusters with the benefits of the long-lasting LED technology. The product offers more energy saving comparing with normal LED candles and lusters, while in the same time it also provide the custome with good light experience with super dimming performance. MASTER Value Glass Led candles and lusters deliver significant energy savings, offering even 30% more compared to normal LED and provides excellent quality of light. By offering a lifetime of 15,000 hours it reduces maintenance costs.

Product data

General Information	
Cap-Base	E14 [E14]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	15000 h
Switching Cycle	20000X
Flux measurement reference	Sphere
Light Technical	
Color Code	922-927 [CCT of 2200K-2700K]
Luminous Flux (Nom)	470 lm
Color Designation	Warm Glow(WG)
Correlated Color Temperature (Nom)	2200 2700 K
Luminous Efficacy (rated) (Nom)	138.00 lm/W


Color Consistency	<6
Color Rendering Index (Nom)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Nom)	3.4 W
Lamp Current (Nom)	24 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.6

MSTER Value GLASS LED candles and lusters

Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	70 °C
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	BA35
Approval and Application	
Energy Efficiency Class	D
Energy Consumption kWh/1000 h	4 kWh

EPREL Registration Number	453150
Product Data	
Full product code	871951432519700
Order product name	MASTER VLE LEDCandleDT3.4-40W E14927BA35CLG
EAN/UPC - Product	8719514325197
Order code	929003013002
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929003013002
Net Weight (Piece)	0.014 kg


Dimensional drawing




Candle BA35 EU 3.5-40W 475lm WG E14 CL

Product	D	C
MASTER VLE LEDCandleDT3.4-40W E14927BA35CLG	35 mm	119 mm

Photometric data




LEDcandle MAS SLR 3,4W BA35 E14 927 CL-GUL



LEDcandle MAS SLR 3,4W B35 E14 927 CL-POC


MSTER Value GLASS LED candles and lusters

Photometric data




LEDcandle MAS SLR BA35 3,4W E14 927 CL-LDD

Lifetime



15K LED



15K LMP

