



# CorePro GLASS LED candles and lusters

## CorePro LEDCandleND 2-25W E14B35 827CL G

Featuring a classic heritage design, Classic filament LED Lamps combine the familiar shapes of classic incandescent bulbs with the benefits of the long-lasting LED technology. An very easy choice for people who are looking for the replacement for retrofit LED candles and lusters, as comparing with convential lamps, it provide 90% energy saving. CorePro Glass LED candles and lusters provides excellent quality of light. By offering a lifetime of 15,000 hours it reduces maintenance costs.

### Product data

General Information	
Cap-Base	E14 [ E14]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	15000 h
Switching Cycle	20000X
Technical Type	2-25W
Flux measurement reference	Sphere
Light Technical	
Color Code	827 [ CCT of 2700K]
Luminous Flux (Nom)	250 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	125.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %


Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Nom)	2 W
Lamp Current (Nom)	20 mA
Wattage Equivalent	25 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.4
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	36 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear

# CorePro GLASS LED candles and lusters

Bulb Shape	B35 [ B 35mm]
<b>Approval and Application</b>	
Energy Efficiency Class	E
Energy Saving Product	Yes
Suitable For Accent Lighting	No
Energy Consumption kWh/1000 h	2 kWh
EPREL Registration Number	387351
<b>Product Data</b>	
Full product code	871951437757800

Order product name	CorePro LEDCandleND 2-25W E14B35 827CL G
EAN/UPC - Product	8719514377578
Order code	929001238392
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001238392
Net Weight (Piece)	0.014 kg


## Dimensional drawing




filament 2.5W-25W 250lm NAD 2700K E14ND

Product	D	C
CorePro LEDCandleND 2-25W E14B35 827CL G	35 mm	97 mm

## Photometric data




LED Lamps, Lightcolour /827 ND CL



Classic LEDCandle ND 2-25W B35 827 CL


# CorePro GLASS LED candles and lusters

## Photometric data




Classic LEDCandle ND 2-25W B35 827 CL

## Lifetime



LEDcandle CLA 4.3-40W E14 B35 Clear 827 ND



LEDcandle CLA 4.3-40W E14 B35 Clear 827 ND

