



CorePro GLASS LED candles and lusters

CorePro LEDCandleND2-25W E14BA35 827CL G

Featuring a classic heritage design, Classic filament LED Lamps combine the familiar shapes of classic incandescent bulbs with the benefits of the long-lasting LED technology. An very easy choice for people who are looking for the replacement for retrofit LED candles and lusters, as comparing with convential lamps, it provide 90% energy saving. CorePro Glass LED candles and lusters provides excellent quality of light. By offering a lifetime of 15,000 hours it reduces maintenance costs.

Product data

General Information		Operating and Electrical	
Cap-Base	E14 [E14]	Input Frequency	50 to 60 Hz
EU RoHS compliant	Yes	Power (Nom)	2 W
Nominal Lifetime (Nom)	15000 h	Lamp Current (Nom)	20 mA
Switching Cycle	20000X	Wattage Equivalent	25 W
Technical Type	2-25W	Starting Time (Nom)	0.5 s
Flux measurement reference	Sphere	Warm Up Time to 60% Light (Nom)	0.5 s
		Power Factor (Nom)	0.4
		Voltage (Nom)	220-240 V
Light Technical		Temperature	
Color Code	827 [CCT of 2700K]	T-Case Maximum (Nom)	36 °C
Luminous Flux (Nom)	250 lm		
Color Designation	Warm White (WW)	Controls and Dimming	
Correlated Color Temperature (Nom)	2700 K	Dimmable	No
Luminous Efficacy (rated) (Nom)	125.00 lm/W		
Color Consistency	<6	Mechanical and Housing	
Color Rendering Index (Nom)	80	Bulb Finish	Clear
LLMF At End Of Nominal Lifetime (Nom)	70 %		

CorePro GLASS LED candles and lusters

Bulb Shape	BA35
Approval and Application	
Energy Efficiency Class	E
Energy Saving Product	Yes
Suitable For Accent Lighting	No
Energy Consumption kWh/1000 h	2 kWh
EPREL Registration Number	387361
Product Data	
Full product code	871951437759200

Order product name	CorePro LEDCandleND2-25W E14BA35 827CL G
EAN/UPC - Product	8719514377592
Order code	929001238492
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001238492
Net Weight (Piece)	0.014 kg


Dimensional drawing




Product	D	C
CorePro LEDCandleND2-25W E14BA35 827CL G	35 mm	123 mm

filament 2.5W-25W 250lm NAD 2700K E14ND

Photometric data




LED Lamps, Lightcolour /827 ND CL



Classic LEDCandle ND 2-25W BA35 827 CL

CorePro GLASS LED candles and lusters

Photometric data



Classic LED Candle ND 2-25W BA35 827 CL

Lifetime



15K LED



15K LMP

