

CorePro GLASS LED candles and lustres

CoreProLED CandleND4.3-40WE14 827B35CLGUK

Featuring a classic heritage design, Classic filament LED lamps combine the familiar shapes of classic incandescent bulbs with the benefits of the long-lasting LED technology. An very easy choice for people who are looking for the replacement for retrofit LED candles and lustres: compared to conventional lamps, it provides a 90% energy saving. CorePro Glass LED candles and lustres provide excellent quality of light. By offering a lifetime of 15,000 hours, they reduce maintenance costs.

Product data


General Information		Operating and Electrical	
Cap base	E14 [E14]	Input frequency	50 to 60 Hz
EU RoHS compliant	Yes	Power (Rated) (Nom)	4.3 W
Nominal lifetime (nom.)	15000 h	Lamp current (nom.)	40 mA
Switching cycle	20,000X	Wattage equivalent	40 W
		Starting time (nom.)	0.5 s
		Warm-up time to 60% light (nom.)	0.5 s
		Power factor (nom.)	0.41
		Voltage (Nom)	220-240 V
Light Technical		Temperature	
Colour Code	827 [CCT of 2,700 K]	T-Case maximum (nom.)	45 °C
Luminous flux (nom.)	470 lm		
Colour designation	Warm white (WW)	Controls and Dimming	
Correlated Colour Temperature (Nom)	2700 K	Dimmable	No
Luminous efficacy (rated) (nom.)	109.00 lm/W	Mechanical and Housing	
Colour consistency	<6	Lamp Finish	Clear
Colour rendering index (nom.)	80		
LLMF at end of nominal lifetime (nom.)	70 %		

CorePro GLASS LED candles and lustres

Bulb shape	B35 [B 35mm]
Approval and Application	
Energy Efficiency Class	F
Energy consumption kWh/1,000 hours	5 kWh
	387402
Product Data	
Full product code	871951434726701

Order product name	CoreProLEDcandleND4.3-40WE14 827B35CLGUK
EAN/UPC – product	8719514347267
Order code	34726701
SAP numerator – quantity per pack	1
Numerator – packs per outer box	10
SAP material	929001889719
SAP net weight (piece)	0.014 kg


Dimensional drawing




Candle B35 4.3-40W 470lm 2700K E14 ND

Product	D	C
CoreProLEDcandleND4.3-40WE14 827B35CLGUK	35 mm	97 mm

Photometric data




LEDcandle CLA 4.3-40W E14 B35 Clear 827 ND



LEDcandle CLA 4.3-40W E14 B35 Clear 827 ND

CorePro GLASS LED candles and lustres


Photometric data




CalcXpert Photometrics 4.5 Philips Lighting B.V. Page 5/7

LEDCandle CLA 4.3-40W E14 B35 Clear 827 ND

Lifetime



LEDCandle CLA 4.3-40W E14 B35 Clear 827 ND



LEDCandle CLA 4.3-40W E14 B35 Clear 827 ND

