



CorePro GLASS LED candles and lusters

CorePro LEDCandle ND 2.2-25W B35 E14 FRG

Featuring a classic heritage design, Classic filament LED Lamps combine the familiar shapes of classic incandescent bulbs with the benefits of the long-lasting LED technology. An very easy choice for people who are looking for the replacement for retrofit LED candles and lusters, as comparing with convential lamps, it provide 90% energy saving. CorePro Glass LED candles and lusters provides excellent quality of light. By offering a lifetime of 15,000 hours it reduces maintenance costs.

Product data

General Information		Power (Nom)	
Cap-Base	E14 [E14]		2.2 W
EU RoHS compliant	Yes	Lamp Current (Nom)	21 mA
Nominal Lifetime (Nom)	15000 h	Wattage Equivalent	25 W
Switching Cycle	20000X	Starting Time (Nom)	0.5 s
Flux measurement reference	Sphere	Warm Up Time to 60% Light (Nom)	0.5 s
		Power Factor (Nom)	0.4
		Voltage (Nom)	220-240 V
Light Technical		Temperature	
Color Code	827 [CCT of 2700K]	T-Case Maximum (Nom)	36 °C
Luminous Flux (Nom)	250 lm		
Color Designation	Warm White (WW)	Controls and Dimming	
Correlated Color Temperature (Nom)	2700 K	Dimmable	No
Luminous Efficacy (rated) (Nom)	113.00 lm/W	Mechanical and Housing	
Color Consistency	<6	Bulb Finish	Frosted
Color Rendering Index (Nom)	80	Bulb Shape	B35 [B 35mm]
LLMF At End Of Nominal Lifetime (Nom)	70 %		
Operating and Electrical			
Input Frequency	50 to 60 Hz		

CorePro GLASS LED candles and lusters

Approval and Application


Energy Efficiency Class	E
Energy Consumption kWh/1000 h	3 kWh
EPREL Registration Number	387381

Product Data

Full product code	871951434679600
Order product name	CorePro LEDCandle ND 2.2-25W B35 E14 FRG

EAN/UPC - Product	8719514346796
Order code	929001345292
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001345292
Net Weight (Piece)	0.012 kg


Dimensional drawing




Candle B35 230V 2-25W 250lm 2700K E14ND

Product	D	C
CorePro LEDCandle ND 2.2-25W B35 E14 FRG	35 mm	97 mm


Photometric data



LEDbulb, Bulb A21 14W, 18W 2200-2700K




LEDbulb 25W E14 827 FR B35




LEDbulb 25W E14 827 FR B35

CorePro GLASS LED candles and lusters

Lifetime



LEDbulb 25W E14 827 FR B35



LEDbulb 25W E14 827 FR B35

