



# CorePro GLASS LED candles and lusters

## CorePro LEDCandleND 2.2-25W BA35 E14 FRG

Featuring a classic heritage design, Classic filament LED Lamps combine the familiar shapes of classic incandescent bulbs with the benefits of the long-lasting LED technology. An very easy choice for people who are looking for the replacement for retrofit LED candles and lusters, as comparing with convential lamps, it provide 90% energy saving. CorePro Glass LED candles and lusters provides excellent quality of light. By offering a lifetime of 15,000 hours it reduces maintenance costs.

### Product data

General Information	
Cap-Base	E14 [ E14]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	15000 h
Switching Cycle	20000X
Flux measurement reference	Sphere

Light Technical	
Color Code	827 [ CCT of 2700K]
Luminous Flux (Nom)	250 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	113.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Input Frequency	50 to 60 Hz

Power (Nom)	2.2 W
Lamp Current (Nom)	21 mA
Wattage Equivalent	25 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.4
Voltage (Nom)	220-240 V

Temperature	
T-Case Maximum (Nom)	36 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	BA35

# CorePro GLASS LED candles and lusters

## Approval and Application

Energy Efficiency Class	E
Energy Consumption kWh/1000 h	3 kWh
EPREL Registration Number	387387

## Product Data

Full product code	871951434685700
Order product name	CorePro LEDCandleND 2.2-25W BA35 E14 FRG

EAN/UPC - Product	8719514346857
Order code	929001345892
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001345892
Net Weight (Piece)	0.014 kg



## Dimensional drawing



Product	D	C
CorePro LEDCandleND 2.2-25W BA35 E14 FRG	35 mm	123 mm


## CandleBA35 230V 2-25W 250lm 2700K E14ND

## Photometric data



## LEDbulb, Bulb A21 14W, 18W 2200-2700K


## LEDbulb 25W E14 827 FR BA35




## LEDbulb 25W E14 827 FR B35

# CorePro GLASS LED candles and lusters

## Lifetime



LEDbulb 25W E14 827 FR B35



LEDbulb 25W E14 827 FR B35

