



MASTER LEDcandle DiamondSpark

MASTER LEDlustre DT 2.8-25W E14 P48 CL

Delivering incandescent-like sparkling light effects, MASTER LEDcandle bulbs are ideal for general and decorative lighting in the hospitality industry, as well as in home environments. The dimmable MASTER LEDcandles drive further efficiencies, while helping to create the desired atmosphere. Mounted in full view in chandeliers, wall scones or modern luminaires, the clear or frosted glass bulbs fit all existing fixtures with an E14 and B15 socket. Drawing upon inputs from chandelier makers and designed to enhance the aesthetic appeal of the chandelier or luminaire, not only when lit but also when not, these lamps come in a classical slender shape with a unique, eye-catching lens design. They produce a beautiful sparkling warm light that delivers huge energy savings and minimizes maintenance cost. The flame-shaped candle lamps comes in a classical slender shape with a unique, eye-catching lens design that perfectly complements modern LED candles.

Product data

| General Information | |
|-------------------------------------|-------------------------------|
| Cap base | E14 [E14] |
| EU RoHS compliant | Yes |
| Nominal lifetime (nom.) | 25000 h |
| Switching cycle | 50,000X |
| | Sphere |
| Light Technical | |
| Colour Code | 822-827 [tunable warm white] |
| Luminous flux (nom.) | 250 lm |
| Colour designation | Warm Glow (WG) |
| Correlated Colour Temperature (Nom) | 2200 2700 K |
| Luminous efficacy (rated) (nom.) | 89.00 lm/W |


| Colour consistency | <6 |
|--|-------------|
| Colour rendering index (nom.) | 80 |
| LLMF at end of nominal lifetime (nom.) | 70 % |
| Operating and Electrical | |
| Input frequency | 50 to 60 Hz |
| Power (Rated) (Nom) | 2.8 W |
| Lamp current (nom.) | 14 mA |
| Wattage equivalent | 25 W |
| Starting time (nom.) | 0.5 s |
| Warm-up time to 60% light (nom.) | 0.5 s |
| Power factor (nom.) | 0.7 |

MASTER LEDcandle DiamondSpark

| | |
|---------------------------------|----------------------------|
| Voltage (Nom) | 220-240 V |
| Temperature | |
| T-Case maximum (nom.) | 80 °C |
| Controls and Dimming | |
| Dimmable | Only with specific dimmers |
| Mechanical and Housing | |
| Lamp Finish | Clear |
| Bulb shape | P48 |
| Approval and Application | |
| Energy Efficiency Class | F |

| | |
|------------------------------------|--|
| Energy consumption kWh/1,000 hours | 3 kWh |
| | 614867 |
| Product Data | |
| Full product code | 871951430606600 |
| Order product name | MASTER LEDlustre DT 2.8-25W E14 P48 CL |
| EAN/UPC – product | 8719514306066 |
| Order code | 30606600 |
| SAP numerator – quantity per pack | 1 |
| Numerator – packs per outer box | 10 |
| SAP material | 929002490702 |
| SAP net weight (piece) | 0.045 kg |


Dimensional drawing




P48 220-240V 2.8-25W 250lm 27-22K E14

| Product | D | C |
|--|-------|-------|
| MASTER LEDlustre DT 2.8-25W E14 P48 CL | 50 mm | 95 mm |

Photometric data




LEDcandle MAS SLR1 2,8W B38 E14 827 CL-POC



LEDLuster MAS SLR1 P48 2,8W E14 827 CL-LDD

MASTER LEDcandle DiamondSpark

Photometric data



General Uniform Lightness
1-1 DIMENSIONAL LIGHT DISTRIBUTION
1-1 DIMENSIONAL LIGHT DISTRIBUTION
Page 1/1

LEDLuster MAS SLR1 2,8W P48 E14 827 CL-GUL

Lifetime



LEDspots LED 25K

LEDspots LMP 25K

