



MASTER LEDcandle DiamondSpark

MASTER LEDlustre DT 2.8-25W E27 P48 CL

Delivering incandescent-like sparkling light effects, MASTER LEDcandle bulbs are ideal for general and decorative lighting in the hospitality industry, as well as in home environments. The dimmable MASTER LEDcandles drive further efficiencies, while helping to create the desired atmosphere. Mounted in full view in chandeliers, wall scones or modern luminaires, the clear or frosted glass bulbs fit all existing fixtures with an E14 and B15 socket. Drawing upon inputs from chandelier makers and designed to enhance the aesthetic appeal of the chandelier or luminaire, not only when lit but also when not, these lamps come in a classical slender shape with a unique, eye-catching lens design. They produce a beautiful sparkling warm light that delivers huge energy savings and minimizes maintenance cost. The flame-shaped candle lamps comes in a classical slender shape with a unique, eye-catching lens design that perfectly complements modern LED candles.

Product data


General Information		Colour consistency	
Cap base	E27 [E27]	Colour consistency	<6
EU RoHS compliant	Yes	Colour rendering index (nom.)	80
Nominal lifetime (nom.)	25000 h	LLMF at end of nominal lifetime (nom.)	70 %
Switching cycle	50,000X	Operating and Electrical	
	Sphere	Input frequency	50 to 60 Hz
Light Technical		Power (Rated) (Nom)	2.8 W
Colour Code	822-827 [tunable warm white]	Lamp current (nom.)	14 mA
Luminous flux (nom.)	250 lm	Wattage equivalent	25 W
Colour designation	Warm Glow (WG)	Starting time (nom.)	0.5 s
Correlated Colour Temperature (Nom)	2200 2700 K	Warm-up time to 60% light (nom.)	0.5 s
Luminous efficacy (rated) (nom.)	89.00 lm/W	Power factor (nom.)	0.7

MASTER LEDcandle DiamondSpark

Voltage (Nom)	220-240 V
Temperature	
T-Case maximum (nom.)	80 °C
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Lamp Finish	Clear
Bulb shape	P48
Approval and Application	
Energy Efficiency Class	F

Energy consumption kWh/1,000 hours	3 kWh
	614862
Product Data	
Full product code	871951430608000
Order product name	MASTER LEDlustre DT 2.8-25W E27 P48 CL
EAN/UPC – product	8719514306080
Order code	30608000
SAP numerator – quantity per pack	1
Numerator – packs per outer box	10
SAP material	929002490802
SAP net weight (piece)	0.045 kg


Dimensional drawing




P48 220-240V 2.8-25W 250lm 27-22K E27 D

Product	D	C
MASTER LEDlustre DT 2.8-25W E27 P48 CL	50 mm	93 mm

Photometric data




LEDcandle MAS SLR1 2,8W B38 E14 827 CL-POC



LEDLuster MAS SLR1 P48 2,8W E27 827 CL-LDD

MASTER LEDcandle DiamondSpark



Photometric data



General Information 41 Philips Lighting B.V. Page 117

LEDLuster MAS SLR1 2,8W P48 E27 827 CL-GUL

Lifetime



LEDspots LED 25K

LEDspots LMP 25K

