



# MASTER LEDcandle DiamondSpark

## MASTER LEDlustre DT 5.5-40W B22 P48 CL

Delivering incandescent-like sparkling light effects, MASTER LEDcandle bulbs are ideal for general and decorative lighting in the hospitality industry, as well as in home environments. The dimmable MASTER LEDcandles drive further efficiencies, while helping to create the desired atmosphere. Mounted in full view in chandeliers, wall scones or modern luminaires, the clear or frosted glass bulbs fit all existing fixtures with an E14 and B15 socket. Drawing upon inputs from chandelier makers and designed to enhance the aesthetic appeal of the chandelier or luminaire, not only when lit but also when not, these lamps come in a classical slender shape with a unique, eye-catching lens design. They produce a beautiful sparkling warm light that delivers huge energy savings and minimizes maintenance cost. The flame-shaped candle lamps comes in a classical slender shape with a unique, eye-catching lens design that perfectly complements modern LED candles.

### Product data

General Information	
Cap base	B22 [ B22]
EU RoHS compliant	Yes
Nominal lifetime (nom.)	25000 h
Switching cycle	50,000X
	Sphere
Light Technical	
Colour Code	822-827 [ tunable warm white]
Luminous flux (nom.)	470 lm
Colour designation	Warm Glow (WG)
Correlated Colour Temperature (Nom)	2200 2700 K
Luminous efficacy (rated) (nom.)	85.00 lm/W


Colour consistency	<6
Colour rendering index (nom.)	80
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	5.5 W
Lamp current (nom.)	26 mA
Wattage equivalent	40 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.9

# MASTER LEDcandle DiamondSpark

Voltage (Nom)	220-240 V
<b>Temperature</b>	
T-Case maximum (nom.)	80 °C
<b>Controls and Dimming</b>	
Dimmable	Only with specific dimmers
<b>Mechanical and Housing</b>	
Lamp Finish	Clear
Bulb shape	P48
<b>Approval and Application</b>	
Energy Efficiency Class	F

Energy consumption kWh/1,000 hours	6 kWh
	614866
<b>Product Data</b>	
Full product code	871951430636300
Order product name	MASTER LEDlustre DT 5.5-40W B22 P48 CL
EAN/UPC – product	8719514306363
Order code	30636300
SAP numerator – quantity per pack	1
Numerator – packs per outer box	10
SAP material	929002491502
SAP net weight (piece)	0.045 kg


## Dimensional drawing



P48 220-240V 5.5-40W 470lm 27-22K B22


Product	D	C
MASTER LEDlustre DT 5.5-40W B22 P48 CL	50 mm	93 mm

## Photometric data



General Uniform Light  
1-1 DIMMABLE 5,5W 827K 27-22K  
Page 10


LEDLuster MAS SLR1 5,5W P48 B22 827 CL-GUL



LEDLuster MAS SLR1 P48 5,5W B22 827 CL-LDD

# MASTER LEDcandle DiamondSpark

## Photometric data




LEDcandle MAS SLR1 5,5W B38 B15 827 CL-POC

## Lifetime



LEDspots LED 25K



LEDspots LMP 25K

