



CorePro GLASS LED candles and lusters

CorePro LEDLusterND4.3-40W E14 827P45FRG

Featuring a classic heritage design, Classic filament LED Lamps combine the familiar shapes of classic incandescent bulbs with the benefits of the long-lasting LED technology. An very easy choice for people who are looking for the replacement for retrofit LED candles and lusters, as comparing with convential lamps, it provide 90% energy saving. CorePro Glass LED candles and lusters provides excellent quality of light. By offering a lifetime of 15,000 hours it reduces maintenance costs.

Product data

General Information	
Cap-Base	E14 [E14]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	15000 h
Switching Cycle	20000X
Flux measurement reference	Sphere

Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux (Nom)	470 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	109.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Input Frequency	50 to 60 Hz

Power (Nom)	4.3 W
Lamp Current (Nom)	35 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.5
Voltage (Nom)	220-240 V

Temperature	
T-Case Maximum (Nom)	55 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	P45 [P 45mm]

CorePro GLASS LED candles and lusters

Approval and Application


Energy Efficiency Class	F
Energy Consumption kWh/1000 h	5 kWh
EPREL Registration Number	387384

Product Data

Full product code	871951434720500
Order product name	CorePro LEDLusterND4.3-40W E14 827P45FRG

EAN/UPC - Product	8719514347205
Order code	929001345592
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001345592
Net Weight (Piece)	0.014 kg


Dimensional drawing




Candle P45 230V 4-40W 250lm 2700K E14ND

Product	D	C
CorePro LEDLusterND4.3-40W E14 827P45FRG	45 mm	80 mm

Photometric data




LEDbulb, Bulb A21 14W, 18W 2200-2700K



LEDbulb 40W E14 827 FR P45


CorePro GLASS LED candles and lusters

Photometric data




LEDbulb 40W E14 827 FR B35

Lifetime



LEDbulb 40W E14 827 FR B35



LEDbulb 25W E14 827 FR B35

