



# CorePro GLASS LED candles and lusters

## CorePro LEDLusterND4.3-40W E27 827P45FRG

Featuring a classic heritage design, Classic filament LED Lamps combine the familiar shapes of classic incandescent bulbs with the benefits of the long-lasting LED technology. An very easy choice for people who are looking for the replacement for retrofit LED candles and lusters, as comparing with convential lamps, it provide 90% energy saving. CorePro Glass LED candles and lusters provides excellent quality of light. By offering a lifetime of 15,000 hours it reduces maintenance costs.

### Product data

General Information	
Cap-Base	E27 [ E27]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	15000 h
Switching Cycle	20000X
Flux measurement reference	Sphere

Light Technical	
Color Code	827 [ CCT of 2700K]
Luminous Flux (Nom)	470 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	109.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Input Frequency	50 to 60 Hz

Power (Nom)	4.3 W
Lamp Current (Nom)	35 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.5
Voltage (Nom)	220-240 V

Temperature	
T-Case Maximum (Nom)	55 °C

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	P45 [ P 45mm]

# CorePro GLASS LED candles and lusters

## Approval and Application


Energy Efficiency Class	F
Energy Consumption kWh/1000 h	5 kWh
EPREL Registration Number	387386

## Product Data

Full product code	871951434722900
Order product name	CorePro LEDLusterND4.3-40W E27 827P45FRG

EAN/UPC - Product	8719514347229
Order code	929001345792
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001345792
Net Weight (Piece)	0.012 kg


## Dimensional drawing




Candle P45 230V 4-40W 250lm 2700K E27ND

Product	D	C
CorePro LEDLusterND4.3-40W E27 827P45FRG	45 mm	78 mm

## Photometric data



LEDbulb, Bulb A21 14W, 18W 2200-2700K




CalcLuX Photonics 4.5 Philips Lighting B.V. Page 1/1

LEDbulb 40W E27 827 FR P45


# CorePro GLASS LED candles and lusters

## Photometric data




LEDbulb 40W E14 827 FR B35

## Lifetime



LEDbulb 40W E14 827 FR B35



LEDbulb 25W E14 827 FR B35

