



CorePro GLASS LED candles and lusters

CorePro LEDLusterND4.3-40W E27 827P45CLG

Featuring a classic heritage design, Classic filament LED Lamps combine the familiar shapes of classic incandescent bulbs with the benefits of the long-lasting LED technology. An very easy choice for people who are looking for the replacement for retrofit LED candles and lusters, as comparing with convential lamps, it provide 90% energy saving. CorePro Glass LED candles and lusters provides excellent quality of light. By offering a lifetime of 15,000 hours it reduces maintenance costs.

Product data

General Information		Power (Nom)	
Cap-Base	E27 [E27]	Lamp Current (Nom)	40 mA
EU RoHS compliant	Yes	Wattage Equivalent	40 W
Nominal Lifetime (Nom)	15000 h	Starting Time (Nom)	0.5 s
Switching Cycle	20000X	Warm Up Time to 60% Light (Nom)	0.5 s
Flux measurement reference	Sphere	Power Factor (Nom)	0.41
		Voltage (Nom)	220-240 V
Light Technical		Temperature	
Color Code	827 [CCT of 2700K]	T-Case Maximum (Nom)	45 °C
Luminous Flux (Nom)	470 lm		
Color Designation	Warm White (WW)	Controls and Dimming	
Correlated Color Temperature (Nom)	2700 K	Dimmable	No
Luminous Efficacy (rated) (Nom)	109.00 lm/W	Mechanical and Housing	
Color Consistency	<6	Bulb Finish	Clear
Color Rendering Index (Nom)	80	Bulb Shape	P45 [P 45mm]
LLMF At End Of Nominal Lifetime (Nom)	70 %		
Operating and Electrical			
Input Frequency	50 to 60 Hz		

CorePro GLASS LED candles and lusters

Approval and Application


Energy Efficiency Class	F
Energy Consumption kWh/1000 h	5 kWh
EPREL Registration Number	387410

Product Data

Full product code	871951434732800
Order product name	CorePro LEDLusterND4.3-40W E27 827P45CLG

EAN/UPC - Product	8719514347328
Order code	929001890592
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001890592
Net Weight (Piece)	0.012 kg


Dimensional drawing




Candle P45 4.3-40W 470lm 2700K E27 ND

Product	D	C
CorePro LEDLusterND4.3-40W E27 827P45CLG	45 mm	82 mm

Photometric data




LEDCandle CLA 4.3-40W E14 B35 Clear 827 ND



LEDCandle CLA 4.3-40W E14 B35 Clear 827 ND

CorePro GLASS LED candles and lusters


Photometric data




CalcXpert Photometrics 4.5 Philips Lighting B.V. Page 5/7

LEDLuster CLA 4.3-40W E27 P45 Clear 827 ND

Lifetime



LEDCandle CLA 4.3-40W E14 B35 Clear 827 ND



LEDCandle CLA 4.3-40W E14 B35 Clear 827 ND

