



# CorePro LEDcandle



## CorePro lustre ND 5-40W E14 827 P45 FR

The frosted CorePro LEDcandle is designed for retrofit replacement of incandescent lamps. It is compatible with fixtures with an E14 holder and is an attractive product for chandeliers. LEDlamps deliver huge energy savings and minimize maintenance cost.

### Product data


General Information		Warm-up time to 60% light (nom.)		0.5 s	
Cap base	E14 [ E14]	Power factor (nom.)		0.51	
EU RoHS compliant	Yes	Voltage (Nom)		220-240 V	
Nominal lifetime (nom.)	15000 h	<b>Temperature</b>			
Switching cycle	50,000X	T-Case maximum (nom.)		81 °C	
	Sphere	<b>Controls and Dimming</b>			
<b>Light Technical</b>		Dimmable		No	
Colour Code	827 [ CCT of 2,700 K]	<b>Mechanical and Housing</b>			
Luminous flux (nom.)	470 lm	Lamp Finish		Frosted	
Colour designation	Warm white (WW)	Bulb shape		P45 [ P 45mm]	
Correlated Colour Temperature (Nom)	2700 K	<b>Approval and Application</b>			
Luminous efficacy (rated) (nom.)	94.00 lm/W	Energy Efficiency Class		F	
Colour consistency	<6	Energy consumption kWh/1,000 hours		5 kWh	
Colour rendering index (nom.)	80				453203
LLMF at end of nominal lifetime (nom.)	70 %	<b>Product Data</b>			
<b>Operating and Electrical</b>		Full product code		871951431264700	
Input frequency	50 to 60 Hz	Order product name		CorePro lustre ND 5-40W E14 827 P45 FR	
Power (Rated) (Nom)	5 W	EAN/UPC – product		8719514312647	
Lamp current (nom.)	44 mA				
Wattage equivalent	40 W				
Starting time (nom.)	0.5 s				

# CorePro LEDcandle

Order code	31264700
SAP numerator – quantity per pack	1
Numerator – packs per outer box	10
SAP material	929002969602

SAP net weight (piece)	0.020 kg
------------------------	----------


## Dimensional drawing




Candle P45 5-40W 470lm 2700K E14 ND FR

Product	D	C
CorePro lustre ND 5-40W E14 827 P45 FR	45 mm	87 mm


## Photometric data



LEDLustre Corepro P45 5W E27 827 FR-LDD



LEDlustre CorePro 5W P45 E14 827-GUL



LEDLustre Corepro 5W P45 E27 827 FR-POC

# CorePro LEDcandle

## Lifetime



15K LED

15K LMP

