



CorePro LEDcandle



Corepro Lustre ND 5-40W E27 827 P45 FR

The frosted CorePro LEDcandle is designed for retrofit replacement of incandescent lamps. It is compatible with fixtures with an E14 holder and is an attractive product for chandeliers. LEDlamps deliver huge energy savings and minimize maintenance cost.

Product data


General Information		Warm-up time to 60% light (nom.)		0.5 s
Cap base	E27 [E27]	Power factor (nom.)	0.51	
EU RoHS compliant	Yes	Voltage (Nom)	220-240 V	
Nominal lifetime (nom.)	15000 h	Temperature		
Switching cycle	50,000X	T-Case maximum (nom.)	79 °C	
	Sphere	Controls and Dimming		
Light Technical		Dimmable	No	
Colour Code	827 [CCT of 2,700 K]	Mechanical and Housing		
Luminous flux (nom.)	470 lm	Lamp Finish	Frosted	
Colour designation	Warm white (WW)	Bulb shape	P45 [P 45mm]	
Correlated Colour Temperature (Nom)	2700 K	Approval and Application		
Luminous efficacy (rated) (nom.)	94.00 lm/W	Energy Efficiency Class	F	
Colour consistency	<6	Energy consumption kWh/1,000 hours	5 kWh	
Colour rendering index (nom.)	80		453202	
LLMF at end of nominal lifetime (nom.)	70 %	Product Data		
Operating and Electrical		Full product code	871951431262300	
Input frequency	50 to 60 Hz	Order product name	Corepro Lustre ND 5-40W E27 827 P45 FR	
Power (Rated) (Nom)	5 W	EAN/UPC – product	8719514312623	
Lamp current (nom.)	44 mA			
Wattage equivalent	40 W			
Starting time (nom.)	0.5 s			

CorePro LEDcandle

Order code	31262300
SAP numerator – quantity per pack	1
Numerator – packs per outer box	10
SAP material	929002969402

SAP net weight (piece)	0.026 kg
------------------------	----------


Dimensional drawing




Candle P45 5-40W 470lm 2700K E27 ND FR

Product	D	C
Corepro Lustre ND 5-40W E27 827 P45 FR	45 mm	88 mm


Photometric data



LEDLustre Corepro 5W P45 E27 827-GUL



LEDLustre Corepro P45 5W E27 827 FR-LDD



LEDLustre Corepro 5W P45 E27 827 FR-POC

CorePro LEDcandle

Lifetime



15K LED

15K LMP

