



CorePro LEDcandle



CorePro lustre ND 7-60W E14 827 P48 FR

The frosted CorePro LEDcandle is designed for retrofit replacement of incandescent lamps. It is compatible with fixtures with an E14 holder and is an attractive product for chandeliers. LEDlamps deliver huge energy savings and minimize maintenance cost.

Product data

General Information	
Cap base	E14 [E14]
EU RoHS compliant	Yes
Nominal lifetime (nom.)	15000 h
Switching cycle	50,000X
	Sphere
Light Technical	
Colour Code	827 [CCT of 2,700 K]
Luminous flux (nom.)	806 lm
Colour designation	Warm white (WW)
Correlated Colour Temperature (Nom)	2700 K
Luminous efficacy (rated) (nom.)	115.00 lm/W
Colour consistency	<6
Colour rendering index (nom.)	80
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	7 W
Lamp current (nom.)	59 mA
Wattage equivalent	60 W
Starting time (nom.)	0.5 s


Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.51
Voltage (Nom)	220-240 V
Temperature	
T-Case maximum (nom.)	87 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Lamp Finish	Frosted
Bulb shape	P48
Approval and Application	
Energy Efficiency Class	E
Energy consumption kWh/1,000 hours	7 kWh
	453214
Product Data	
Full product code	871951431304000
Order product name	CorePro lustre ND 7-60W E14 827 P48 FR
EAN/UPC – product	8719514313040

CorePro LEDcandle

Order code	31304000
SAP numerator – quantity per pack	1
Numerator – packs per outer box	10
SAP material	929002973102

SAP net weight (piece)	0.023 kg
------------------------	----------


Dimensional drawing




Candle P48 7-60W 806lm 2700K E14 ND FR

Product	D	C
CorePro lustre ND 7-60W E14 827 P48 FR	48 mm	93 mm


Photometric data



LEDlustre CorePro P48 7W E27 827 FR-LDD



LEDlustre CorePro 7W P48 E27 827 FR-POC



Page 10

LEDlustre CorePro 7W P48 E14 827-GUL

CorePro LEDcandle

Lifetime



15K LED

15K LMP

