

2267795-4 ✓ ACTIVE

TE Internal #: 2267795-4

Pluggable I/O Cable Assemblies, Pluggable / Direct Attach, 24
AWG Wire Size, .25 mm² Wire Size, Length .246 ft [.075 m], Black, 0
Power Positions

[View on TE.com >](#)



Cable Assemblies > Copper Cable Assemblies > Pluggable I/O Cable Assemblies



Pluggable I/O Cable Assembly Type: **Pluggable / Direct Attach**

Wire Size: **.25 mm²**

Pluggable I/O Cable Assembly Shielded: **No**

Cable Assembly Length: **.075 m [.246 ft]**

Features

Product Type Features

| | |
|--|---------------------------|
| Latching Style | Pull Tab Release |
| Product Type | Cable Assembly |
| Product Designation | Patch Cord |
| Cable Assembly Category | Industry Standard |
| Pluggable I/O Cable Assembly Type | Pluggable / Direct Attach |
| Pluggable I/O Cable Assembly Shielded | No |
| Pluggable I/O Cable Assembly Cable Style | Discrete Pairs |

Configuration Features

| | |
|------------------------------------|--------------|
| Configuration | Double-Ended |
| Number of Power Positions | 0 |
| Pluggable I/O Cable Assembly Keyed | No |

Body Features

| | |
|------------------------------------|-------|
| Pluggable I/O Cable Assembly Color | Black |
|------------------------------------|-------|

Contact Features

| | |
|--------------------------------------|------|
| Contact Mating Area Plating Material | Gold |
|--------------------------------------|------|



Mechanical Attachment

| | |
|-----------|---------|
| Jackscrew | Without |
|-----------|---------|

Housing Features

| | |
|------------------|---------------|
| Housing Material | Thermoplastic |
|------------------|---------------|

Dimensions

| | |
|-----------|---------------------|
| Wire Size | .25 mm ² |
|-----------|---------------------|

Operation/Application

| | |
|--------------|----|
| Halogen Free | No |
|--------------|----|

Other

| | |
|-----------------------|------------------|
| Cable Assembly Length | .075 m [.246 ft] |
|-----------------------|------------------|

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

| | |
|---|---|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUL 2021 (219) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC |
| Halogen Content | Not Low Halogen - contains Br or Cl > 900 ppm. |
| Solder Process Capability | Not reviewed for solder process capability |


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Customers Also Bought



Documents

Product Drawings

CA, MTE FOW-FOW, 5POS, 75mm 15Au, 24AWG

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_2267795-4_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2267795-4_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2267795-4_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.



Datasheets & Catalog Pages

[Datasheet - Ampmodu Mte Off-The Shelf Cable Assemblies](#)

English

[Circular Plastic Connectors Standard Cable Assemblies](#)

English

Product Specifications

[Application Specification](#)

English