


Miniature & Subminiature Condenser Microphones

Lavaliere Microphone

- ① Clip
- ② Windscreen
- ③ 4 Pin Mini XLR
- ④ 3 Pin Mini XLR (Option)
- ⑤ 3.5mm Stereo Plug (Option)
- ⑥ 4 Pin Hirose Connector (Option)



***Note : above ④、⑤ and ⑥ are standard accessory to deluxe pack.**




CM-201iF/CM-201iB

Miniature Lavaliere Microphone

- * Omni-directional pick up pattern for various applications.
- * Wide dynamic range and frequency response for excellent sound reinforcement.
- * No proximity effect.
- * Low profile design.
- * Together with clip for easy attaching to a tie, lapel, dress etc.
- * Detachable connector.

Available Color



Model No.	CM-201i
Frequency Response	60 ~ 15,000Hz
Polar Pattern	Omni-directional
Sensitivity @ 1 KHz	-60 ± 3dB *(1mV)*0dB=1V/μbar
Impedance	2.2kΩ
max. SPL for 1% T.H.D.	130dB
Connector Type	4 Pin Mini XLR
Standard Accessories	Windscreen
Dimension (mm)	Ø5mm (W) * 9mm (H)
Net Weight	20.7 grams

CM-125iF/CM-125iB

Subminiature Lavaliere Microphone

- * World class quality.
- * For theatre, documentary, TV and live sound.
- * Omni-directional.
- * Excellent acoustic performance.
- * Ultra slim design.
- * Detachable connector.

Available Color



Model No.	CM-125i
Frequency Response	50 ~ 18,000Hz
Polar Pattern	Omni-directional
Sensitivity @ 1 KHz	-53 ± 3dB *(2.24mV)*0dB=1V/μbar
Impedance	4.4kΩ
max. SPL for 1% T.H.D.	130dB
Connector Type	4 Pin Mini XLR
Standard Accessories	Windscreen
Dimension (mm)	Ø4mm (W) * 11mm (H)
Net Weight	7 grams (cable excluded)

Miniature & Subminiature
Condenser Microphones