

# Ultra Slim Portable DVD Writer

**8X** 14.6 mm  
Ultra Slim and Light

SDRW-08V1M-U

ASUS SDRW-08V1M-U is an ultra slim DVD writer at just 14.6 mm. It is a slim external DVD drive with an integrated, self-storing USB cable. To provide user-friendly connection, it supports USB Type-C interface to allow data transmission including PC and Mac.

## FEATURES

### Clever Cable-Storage Design

*Easily conceals or releases 24cm Type-C cable*

### M-DISC Support

*Save users' data for up to 1,000 years*

### Disc Encryption\*

*Protect users' data with password control and encoded file name functionality*

### Nero BackItUp\*

*Full backup for your devices*



## SPECIFICATIONS

### Color

Black

### Read Speed

DVD±R: 8X  
DVD+R(SL, M-DISC): 8X  
DVD±RW: 8X  
DVD-ROM: 8X  
DVD±R(DL): 8X  
DVD-ROM(DL): 8X  
CD-R/ROM/RW: 24X  
DVD-Video Playback: 4X  
Audio CD Playback: 10X

### Write Speed

DVD±R: 8X  
DVD+R(SL, M-DISC): 4X  
DVD±RW: 8X  
DVD-RW: 6X  
DVD±R(DL): 6X  
CD-R/RW: 24X

### Access Time (Random)

DVD: 170 ms  
CD: 160 ms

### O/S Compatibility

Windows® 11/10/8.1  
Mac OS® X 10.6 and above

### Bundled Software (For Windows OS)

CyberLink Power2Go 8  
CyberLink PowerBackup 2.6  
Nero BackItUp  
E-Green

### Writing Mode

(1) DVD-R: Disc at Once and Incremental Recording  
(2) DVD-R DL: Disc at Once and Incremental Recording  
(3) DVD-RW: Disc at Once, Incremental Recording and Restricted Overwriting  
(4) DVD+R: Sequential Recording  
(5) DVD+R DL: Sequential Recording  
(6) DVD+RW: Random Recording  
(7) CD-R/RW: Disc at Once, Session at Once, Track at Once and Packet Recording

### System Requirement

CPU: Intel® Pentium® 4 2.0 GHz or AMD Athlon™ 2100+ or higher  
RAM: 512 MB or more is recommended  
HDD: 10 GB or more

### Disc Formats

#### Reading:

DVD±R(SL/DL), DVD±RW, DVD-ROM(SL/DL), DVD-Video, CD-R, CD-RW, CD-ROM, Audio CD, VCD, CD-I, CD-Extra, Photo CD, CD-text, CD-ROM/XA, Multi-session CD

#### Writing:

DVD±R(SL/DL), DVD±RW, CD-R, CD-RW

## Configurations

### Dimensions

150 x 142 x 14.6 mm (L/W/H)

### Weight

255 ± 20 g

### Interface

USB Type-C

### Disc Diameters

12 cm and 8 cm

## Electrical and Environmental Specifications

### Power Requirement

USB Power +5V ± 5%

### Temperature

Operating: 5° C to 40° C  
Storage: -30° C to 60° C

### Humidity


Operating: 15%~80% (Non-condensing)  
Storage: 10%~90% (Non-condensing)

\*This feature is for Windows OS only


# Package Contents



Optical Drive



QIG  
(Quick Installation Guide)




Software



## Clever Cable-Storage Design

### Hidden USB Type-C Cable

Easily conceals or releases 24cm Type-C cable.



## Disc Encryption\*

### Double Security On-the-Go

Hassle-free data protection through password control and hidden-folder functions.



1 / copy the file

2 / create hidden,  
password-protected  
folders

3 / encryption

\*This feature is for Windows OS only



## Backup Software Included\*

### Full Backup for Your Devices

Nero BackItUp enables easy archival of photos, videos or data to your HDD or SSD.



1 / Select backup target

2 / set a schedule

3 / auto backup

\*This feature is for Windows OS only



## Drag and Burn\*

### 3 Easy Steps to Complete Disc Burning

Create a disc in just three easy steps, via intuitive interface.



1 / drag and drop  
to the thumbnail

2 / burn

3 / done

\*This feature is for Windows OS only