

CKG57NX7R1H476M500JJ

TDK Item Description : CKG57NX7R1H476MT***




Application & Main Feature

Automotive Grade (MEGACAP Type)

Series

CKG57N(5750) [EIA CC2220]



Dimensions

L 6.00mm +/-0.5mm
 W 5.00mm +/-0.5mm
 T 5.00mm +/-0.5mm
 E 1.60mm +/-0.3mm

Temperature Characteristic

X7R (-55 to 125 degC +/-15%)

Rated Voltage

1H (50Vdc)

Capacitance

47uF

Capacitance Tolerance

M (+/-20%)

Dissipation Factor

5% Max.






Insulation Resistance

10Mohm Min.

AEC-Q200

Yes

Characterization Sheet (Multilayer Ceramic Chip Capacitors)



⚠ All specifications are subject to change without notice.