

X5C8000VM-G**3 YEAR Warranty** 

Part Number: X5C8000VM-G
Product Group: CCTV
Product Type: IP Dome Camera

**8MP (4K) AI IP Motorised Vandal Eyeball/Turret Dome Camera**

Style	IP Dome Camera
Weather Resistant	Yes (IP66)
Vandal Resistant	Yes
Mounting Type	Wall or Ceiling
Sensor	1/2.8" Progressive CMOS
On Board Camera Functions	Automatic White Balance, Automatic Gain Control, Automatic Electronic Iris, 3D DNR, Starlight, Backlight Compensation, Privacy Masking, Motion Detection, WDR
Video Analytics Functions	Perimeter Intrusion Detection, Line Crossing Detection, Pedestrian Detection, Vehicle Detection, Face Detection
Resolution	8MP (3840 x 2160)
Lens Type	Varifocal
Lens Size	2.7-13.5mm
Viewing Angle	30-116°
Night Vision	60m Smart IR
Minimum Illumination	Colour 0.1lux @ F1.2 (AGC ON); B/W 0 lux @ IR ON

Video Compression	H.265/H.264
Video Streams	Triple Stream (Main/Sub/Mobile)
Video Resolution	Main Stream: 8MP (3840x2160), 5MP (2592x1944,3072x1728), 4MP (2592x1520), 3MP (2304x1296), 1080P (1920x1080), 960P (1280x960), 720P (1280x720) Sub Stream: 720P (1280x720), VGA (640x480), QVGA (320x240) Mobile Stream: VGA (640x480), QVGA (320x240)
Max. Framerate	25fps
Video Bitrate	8Kbps - 16Mbps
Network Connection	RJ45 Socket (10/100)
Network Protocols Supported	TCP/IP, HTTP, DHCP, DNS, DDNS, RTP/RTSP, SMTP, NTP, UPnP, SNMP, HTTPS, FTP
Onvif	Profile S/G/T
Power Over Ethernet (PoE)	Yes
Audio Input	1 Input (RCA), 1 Output (RCA)
Power Input	12V DC Socket/POE (IEEE802.3af)
On Board Recording	Yes - Micro SD Card (Max 256GB)
Alarm Input	1 Input, 1 Output
Video Analytics	Yes
Operating Temperature	-30 to 55°
Dimensions (WHD)	Ø126 x 102.51mm
Weight (kg)	0.96
Warranty	3 Year Warranty

Accessories

Junction Box (Model: JB-004)



Junction Box (Model: JB-006)



Wall Bracket (Model: WB-006)

