

V-TUF SE130 - 130BAR ELECTRIC PRESSURE



SPECIFICATION

MAX PRESSURE	130 BAR
WORKING PRESS.	120 BAR
FLOW(L/MIN)	9 MAX
PUMP TYPE	SELF-PRIMING
VOLTAGE	240
TOTAL STOP SYSTEM	YES
CHEMICAL APPLICATION	YES
MOTER TYPE	INDUCTION
POWER RATING	2800W
HIGH PRESSURE HOSE	9M HIGH PRESSURE
GUNANDLANCEKIT	YES
NOZZLES	VARIO JET
WEIGHT	21.5 KG

**130
BAR**
MAX
PRESSURE

**TOTAL
STOP
SYSTEM**
SAVE
ELECTRICITY

**LOW
AMP
USAGE**

FEATURES

Roll Cage Enclosed Pressure Washer
Easy to replace spares
TOTAL STOP SYSTEM
9M High pressure Hose

WHY BUY?

POWERFULL 130BAR MAX CLEANING PERFORMANCE
SELF-PRIMING PUMP ALLOWS FOR SUCTION FROM SEPARATE
IBC OR BARREL
THE ROBUST ROLL CAGE DESIGN FOR EXCELLENT
PROTECTION & PORTABILITY
LOW AMP USAGE - RELIABLE STARTUP

ItemNo.	Description
SE130	130BAR MEDIUM DUTY ELECTRIC PRESSURE WASHER

V-TUF.COM

T+44(0) 152251 57 67

E ENQUIRIES@V-TUF.COM