



## TSC 30 Fibre patch cord 30m SC

Art. Number 307015



### Fibre Optic patch cord

The **TSC xx patch cord** is a single mode cable terminated with SC/APC connector plugs at both ends. It is recommended for indoor installations in cable ducts and cabinets of fibre optic networks used for applications like:

- CATV distribution and DOSIS data transmission
- SAT-IF and DTT distribution
- Other fibre optic communication systems

## Technical Specifications

### ORDER INFORMATION

EAN Number 5702663070158

### OPTICAL CHARACTERISTICS

Fibre type G.652.D  
Optical Attenuation 1310/1550 | dB/km 0.3 dB/km  
Optical cabletype Single-mode

### CONSTRUCTION

Jacket – dimension | mm 3.0 mm  
Jacket - material LSZH

### CHARACTERISTICS

Wavelength | nm 1310...1550 nm

### RETURN LOSS

Return Loss | dB >60 dB

### OPERATIONAL

Temperature - operating | °C -40...+80 °C

### CONNECTORS

Connector Type Optical - SC/APC



## Technical Specifications

### MECHANICAL

Cable length   m	30 m
Colour	Yellow
Packaging Depth   m	0.000 m
Packaging Height   m	0.000 m
Total Weight   kg	0.671 kg
Packaging Width   m	0.000 m
Minimum bending radius   mm	50 mm
Net Weight   kg	0.666 kg
Tara Weight   kg	0.005 kg
Packaging Volume   m3	0.000 m3