


## Specifications

## ABT-410-RC

|                                  |           |
|----------------------------------|-----------|
| Rated voltage (Vp-p square wave) | 1.5Vp-p   |
| Operating voltage                | 1~3Vp-p   |
| Rated current at rated voltage   | ≤15mA     |
| Sound output at 2048Hz at 10cm   | ≥80dB     |
| Resonant frequency               | 2048Hz    |
| Coil resistance                  | 42±6Ω     |
| Coil impedance at 2048Hz         | 120Ω      |
| Operating temperature            | -20~+70°C |
| Storage temperature              | -30~+80°C |
| Weight                           | 2g        |

Requires additional electronic circuitry to operate as a sounder. Not wave solderable.



## Features

- ROHS compliant
- Low current consumption
- PCB mountable

All data at 25°C unless otherwise specified

**Dimensions** Unit: mm Tolerance: ±0.5mm



ALAN BUTCHER COMPONENTS LTD

## Alan Butcher Components Ltd

Unit 1 Beechwood Clump Farm Industrial Estate Tin Pot Lane Blandford Dorset DT11 7TD

Telephone 01258 456360 Facsimile 01258 459194 Email sales@abcomponents.co.uk

[www.abcomponents.co.uk](http://www.abcomponents.co.uk)