



### Main

Range of Product	EZ meter-pak
Product or Component Type	Meter center main unit
Main type	Main Circuit Breaker
Included Items	Closing plate Circuit-breaker3P 1200 A

### Complementary

Main rated current	1200 A
Bus rated current	1200 A
Material	Aluminium busbar
Enclosure Material	Steel
[Ue] rated operational voltage	208Y/120 V AC
Device mounting	Surface
Number of Phases	3 phase in 3 phase out
Service feed location	UG
Electrical connection	Lugs 1 AWG 6...300 kcmil aluminium/copper) ground Studs 3line Studs 3neutral
Wiring configuration	4-wire
Height	66.20 in (1681.48 mm)
Width	32.39 in (822.71 mm)
Depth	13.69 in (347.73 mm)

### Environment

Product certifications	UL Listed EUSERC
Enclosure Rating	NEMA 3R

### Ordering and shipping details

Category	00020-EZ METER-PAK
Discount Schedule	DE4
GTIN	785901939511
Package weight(Lbs)	432.00 lb(US) (195.952 kg)
Returnability	Yes
Country of origin	MX

### Packing Units

Package 1 Height	2.17 ft (0.660 m)
Package 1 width	3.55 ft (1.082 m)
Package 1 Length	6.32 ft (1.925 m)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>

## Contractual warranty

Warranty	18 months
----------	-----------