

acer



PROJECTING THE FUTURE BUSINESS

Acer P1357Wi

- 4,500 lumens brightness
- Acer Bluelight Shield
- Acer LumiSense
- 20,000:1 Dynamic Black
- Wireless hidden dongle display



Wireless Projection



Brightness



BluelightShield™



LUMISENSE



ColorSafe II



ColorBoost 3D

Feature Highlights

Expressive display

- WXGA (1,280 x 800)
- 4,500 ANSI lumens
- Dynamic Black 20,000:1
- Acer BlueLight Shield
- Acer LumiSense
- Acer ColorBoost3D
- Acer ColorSafe II
- HDMI 3D

Enhanced usability

- Wireless projection frees you from cable chaos (Default)
- 10W built-in speaker
- AC power on

Installation flexibility

- +/-40° (Vertical, Manual & Auto) Keystone
- Auto ceiling-mounted correction

Eco-friendly functionality


- Acer EcoProjection
- Lamp life up to 15,000 hours in ExtremeEco mode

P1357Wi

- Part Number: MR.JUP11.001

- EAN Code: 4710886649588

Model name	P1357Wi
Projection system	DLP™
Resolution	Native WXGA (1,280 x 800) Maximum WUXGA (1,920 x 1,200)
Brightness	4,500 ANSI Lumens (Standard), 3,200ANSI Lumens (ECO) (Compliant with ISO 21118 standard)
Aspect ratio	16:10 (Native), 4:3/16:9 (Supported)
Contrast ratio	Dynamic Black 20,000:1
Throw ratio	1.21 ~ 1.57 (77" @ 2 m)
Projection lens	F = 2.59 ~ 2.87, f = 16.88 mm ~ 21.88 mm, Manual Zoom and Manual Focus
Keystone correction	+/-40° (Vertical, Manual & Auto)
Lamp life	5,000 Hours (Standard), 10,000 Hours (ECO), 15,000 Hours (ExtremeEco)
Noise level	31 dBA (Standard), 26 dBA (ECO)
Input interface	Analog RGB/Component Video (D-sub) x 1 Composite Video (RCA) x 1 HDMI1.4a (Video, Audio, HDCP1.4) x 2 PC Audio (Stereo mini jack) x 1 USB (Wireless dongle, Type A) x 1
Output interface	Analog RGB (D-sub) x 1 PC Audio (Stereo mini jack) x 1 DC Out (5V/1A, USB Type A) x 1
Control	RS-232 (mini DIN) x 1
Dimensions	299.5 x 220 x 105.1 mm (11.8" x 8.7" x 4.1", with feet)
Weight	2.4 Kg (5.29 lbs)



Standard Accessory



Optional Accessory

