




BU-T4171110405002-0.2M

(Receptacle, Rear Mount, 5-Position Female Straight-Open End, 22 AWG, .2M)



Panel hole size



Panel thickness

Pin Out

J1	COLOR	J2
1	BROWN	OPEN
2	WHITE	
3	BLUE	
4	BLACK	
5	GRAY	

- Mueller's BU-T4171110405002-0.2 is a cable assembly that has a 5-position rear mount female receptacle to open end, 22 AWG, .2 Meters.
- Shell size for connector: M12 (B Coding)
- Cable Material: UL 1007 22AWG Hook Up Wire
 - Overall length = 0.656' (0.2M)
- Coupling Nut Material: Anodized Aluminum
- Rating:
 - Voltage: 60V AC/DC
 - Current: 4 Amps
 - Ambient Temperature: -25°C to 85°C
- Standard: IEC 61076-2-101
- Waterproof: IP67/IP68
- RoHS 3 Compliant