

Perfect for under cabinet domestic and some light commercial applications.

EternaPro
LED
5 YEAR
Warranty*

PERFECT FOR UNDER CABINET DOMESTIC APPLICATIONS

LED SUPER FLAT STRIP LIGHTS


Ultra low power consumption with excellent light output. The inclusion of a link lead and butt connector allows continuous linear, spaced linear or radial installations.

- Aluminum and polycarbonate construction
- Ultra-bright warm white LEDs for a pleasing lighting effect (3000K colour temperature)
- Super flat design
- **9 LED** strip output: 1.8W / total circuit wattage (with driver): 2.80W
- **15 LED** strip output: 3W / total circuit wattage (with driver): 4.38W
- Reeded diffuser for soft diffused light
- Fixing clips included for under-cabinet or wall installation
- 300mm link lead and butt connector included: allowing flexible linking options


36W CONSTANT VOLTAGE DRIVER (SFLDR36)

- For use with SFLWW range only
- Allows multiple strip lights to be linked
- Includes 0.5m mains cable & 2m fitting supply cable with amp-plug connector: easy installation
- Allows any combination of SFLWW9 & SFLWW15 upto a maximum power load of 36W: simply link the first fitting to the driver and subsequent fittings to each other


- **Strip lights** = M.O.M: 1 / O.P.Q: 10
- **Driver** = M.O.M: 1 / O.P.Q: 20




SUPER FLAT PROFILE



2 x surface mounting clips and 2 x horizontal mounting clips included



Butt connector included



300mm link lead included



Driver


2m fitting supply cable with amp-plug connector

Eterna
Everyday Lighting For Professionals

Code	Version	Colour	Rated Wattage	Colour Temp.	Lumens	Avg. Rated Life (Hrs)	IP Rating	Energy Rating
SFLWW9	9 LED	Matt Silver	1.8W	3000K	160 lm	20,000 hrs	IP20	A+
SFLWW15	15 LED		3W		290 lm			
SFLDR36	36W Driver							

Eterna SFLWW9 / 15

This luminaire contains built-in LED lamps.



The lamps cannot be changed in the luminaire.

874/2012



SPECIFICATIONS:	SFLWW9	SFLWW15
Lumens total flux	160 lm	290 lm
Lumens 120° flux	150 lm	280 lm
Rated Wattage	1.8W	3W
Rated luminous flux	150 lm	280 lm
Nominal life time of the lamp	20,000 hrs	20,000 hrs
Colour temperature	3000K	3000K
Number of switching cycles before premature lamp failure	10,000	10,000
Warm-up time up to 60 % of the full light output	Instant full light	Instant full light
Dimmable	No	No
Lamp dimensions (mm)	350 x 18.6	550 x 18.6
Nominal beam angle	120°	120°
Rated power	1.8W	3W
Rated lamp lifetime	20,000	20,000
Lamp power factor	0.9	0.9
Lumen maintenance factor at end of nominal life	70%	70%
Starting time	<0.5s	<0.5s
Colour rendering	80	80
Colour consistency	Within 6 step Macadam ellipse	Within 6 step Macadam ellipse
Rated peak intensity	132cd	246.4cd
Rated beam angle	120°	120°

*Subject to terms & conditions