



TECHNICAL INFORMATION

Watts:	12
Lumens:	1440
Shape:	Round
Input Power:	AC:220-240V, 50/60Hz
Long Life:	30,000 Hours
Unit Color:	White
Body Type:	PC
LED Chip Type:	SMD-Samsung Chip
CRI:	>80
Operation Temperature:	-20°C to +45°C
Dimmable:	No
Beam Angle:	110°
Color Temperature:	4000K
Dimension:	Ø270x75mm
Type:	Light
LED Chip Solution:	6V 150mA

SLIM DOME | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 820 - 1295 940

[View more details](#)

STYLISH & MODERN DESIGN

Slim and sleek appearance with round and circular edges that goes well with any contemporary interior or outdoor areas



FEATURES

- Fitted with high efficiency Samsung LED Chips that offer up to 85% in energy savings
- Efficient thermal management technology
- 100% PC for endurance & durability
- IP54 rated protection
- Suitable for open areas constantly exposed to dust and moisture like parking lots, corridors, airports, and malls

CE/EMC

CE/LVD



PACKAGING

Gross Weight (Kgs): 0.775
Unit CBM: 0.006272
Dimension: Ø270x75mm

MASTER BOX PACKAGING

Box Qty: 10
Qty Per Pallet: 240
Length (Box) mm: 80
Width (Box) mm: 280
Height (Box) mm: 280

LISTING DETAILS

Commodity Code: 9405114090
Ean Code: 3800157641449