



TECHNICAL INFORMATION

Watts:	12
Lumens:	1440
Shape:	Round
Input Power:	AC:220-240V, 50/60Hz
Long Life:	30,000 Hours
Unit Color:	White
Body Type:	PC
LED Chip Type:	SMD-Samsung Chip
CRI:	>80
Operation Temperature:	-20°C to +45°C
Dimmable:	No
Beam Angle:	110°
Color Temperature:	4000K
Dimension:	Ø270x75mm
Sensor Type:	Microwave
Detection Distance:	3-6m, 6-10m and optional

SLIM DOME SENSOR | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 821 - 1295 940

[View more details](#)



FEATURES

- Fitted with high efficiency Samsung LED Chips that offer up to 80% in energy savings
- Slim bulkheads are equipped with emergency battery and microwave sensor
- (3) hrs on emergency situations - Maintained operation
- Microwave sensor featuring - manual override, dimmable, day light sensor & corridor function
- DIP switch sensor setting allowing flexible sensor settings
- Suitable for open areas constantly exposed to dust and moisture like parking lots, corridors, airports, and malls

PACKAGING

Gross Weight (Kgs): 0.7
Unit CBM: 0.006272
Dimension: Ø270x75mm

MASTER BOX PACKAGING

Box Qty: 10
Qty Per Pallet: 200
Length (Box) mm: 280
Width (Box) mm: 280
Height (Box) mm: 80

LISTING DETAILS

Commodity Code: 9405114090
Ean Code: 3800157641456

CE/EMC

CE/LVD

