



BULKHEAD EMERGENCY PACK-CCT | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 20095 - 931 940

[View more details](#)

TECHNICAL INFORMATION

Watts:	20
Lumens:	1850
Shape:	Round
Input Power:	AC:200-240V, 50/60Hz
Long Life:	30,000 Hours
Unit Color:	White
Body Type:	PC
PF:	>0.5
LED Chip Type:	SMD-Samsung Chip
CRI:	>80
Beam Angle:	120°
Color Temperature:	31N1
Dimension:	380x78mm
Emergency Standby Watts:	1.5
Battery Type:	Ni-CD, 9.6V 1.0Ah Battery
Battery Charging Current:	30mA



FEATURES

- Uses High Quality Power Driver and Samsung LED Chip
- Built-in switch for CCT changing
- Hinged LED gear tray for easy installation
- Emergency backup for more than 3 Hours
- Withstands weather, dust and vandalism
- Applications - Passage, Exterior walls, Airport, Malls, Security Lighting etc



PACKAGING

Gross Weight (Kgs): 1.68
Unit CBM: 0.01395
Dimension: 380x78mm

MASTER BOX PACKAGING

Box Qty: 10
Qty Per Pallet: 120
Length (Box) mm: 390
Width (Box) mm: 83
Height (Box) mm: 390

LISTING DETAILS

Commodity Code: 9405104090
Ean Code: 3800157657440