



### TECHNICAL INFORMATION

Watts:	9
Lumens:	806
Shape:	A60
Input Power:	AC:220-240V, 50Hz
Long Life:	30,000 Hours
Unit Color:	White
Body Type:	Thermoplastic
PF:	>0.5
LED Chip Type:	SMD
CRI:	>80
Operation Temperature:	-25°C to +50°C
Dimmable:	No
Beam Angle:	200°
Color Temperature:	6400K
Equivalence Watts:	60
Dimension:	Ø60x104mm

### GLS B22 | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

*One brand. endless solutions..*

SKU: 7403 - 1552 940

[View more details](#)

**B22**  
THERMOPLASTIC BULB



**SMD LED'S**



**80%**  
ENERGY  
SAVING



**B22**  
HOLDER



**IP20**  
RATING



**2 YEAR**  
WARRANTY



SAVE UP TO  
**80%**  
ENERGY



**CRI > 80**



**A+**  
ENERGY  
RATING

### FEATURES

- Modern LED SMD technology for better reliability and durability
- Replaces 60 watts old halogen lamp
- Lasts hours, longer life span than Standard halogen lamps
- Designed for B22 standard holder
- Suitable for residential lighting, commercial lighting, decorative, living rooms, lounges etc.

CE/EMC

CE/LVD



### PACKAGING

Gross Weight (Kgs): **0.05**  
Unit CBM: **0.000378**  
Dimension: **Ø60x104mm**

### MASTER BOX PACKAGING

Box Qty: **10**  
Qty Per Pallet: **2500**  
Length (Box) mm: **60**  
Width (Box) mm: **60**  
Height (Box) mm: **110**

### LISTING DETAILS

Commodity Code: **8539500000**  
Ean Code: **3800157629287**