



- Full metal enclosure
- Plug in insulated busbar assembly
- 18W Main switch only

**Product Specification Data**

Revision Date: 15/10/2021

Mounting method	Surface mounted (plaster)
Number of phases	1
Protection	Miniature- / earth leakage circuit breaker
Total number of groups	1
Number of poles main switch	2
Main switch rated current	100 A
Over voltage protection	No
Material housing	Steel
Degree of protection (IP)	IP2XC
Height	261 mm
Width	438 mm
Width in number of modular spacings	20
Depth	121 mm
Extension possible	No
With transparent cover	No
Lockable	Yes
Product Standard/s	BS EN 61439-3
Frequency	50 Hz
CE Conformity	Yes
WEEE Symbol	Yes
UKCA Conformity	Yes
Amperage	100 A
Operating Voltage	230 V
Type of Current	AC
Consumer Unit Type	Main switch only
Total final circuit modular ways	18
Busbar type	Plug in
Main switch rating	100 A
Main switch final circuit modular ways	18

Colour RAL

9010

Although every effort has been made to ensure accuracy in the compilation of the technical detail within this datasheet, specifications and performance data are constantly changing. Latest details can be obtained from the Electrium website.

The logo for Electrium, featuring the word "electrium" in a bold, lowercase, sans-serif font. Below the text is a horizontal bar composed of four colored segments: green, red, blue, and yellow.

**Electrium Sales Limited**, Walkmill Lane, Cannock WS11 0XE  
01543 455000 [www.electrium.co.uk](http://www.electrium.co.uk) [info@electrium.co.uk](mailto:info@electrium.co.uk)