

X4C5000VM-W-3**3 YEAR Warranty** 

Part Number: X4C5000VM-W-3

Product Group: CCTV

Product Type: IP Dome Camera

**5MP IP Motorised Vandal Eyeball/Turret Dome Camera**

Style	Eyeball/Turret Dome Camera
Weather Resistant	Yes (IP66)
Vandal Resistant	Yes
Mounting Type	Wall or Ceiling
Sensor	1/2.7" Progressive CMOS
On Board Camera Functions	Automatic White Balance, Automatic Gain Control, Automatic Electronic Iris, 3D DNR, Starlight, Backlight Compensation, Privacy Masking, Motion Detection, WDR, Smart IR
Resolution	5MP (2592 x 1944)
Lens Type	Motorised Auto Focus
Lens Size	2.7-13.5mm
Viewing Angle	30-116°
Night Vision	60m Smart IR
Minimum Illumination	Colour 0.05lux @ F1.2 (AGC ON); B/W 0 lux @ IR ON
Video Compression	H265/H264

Video Streams	Triple Stream
Video Resolution & Frame Rates	Main Stream - 5MP (2592x1944), 4MP (2592x1520), 3MP (2304x1296), 1080P (1920x1080), 720P (1280x720), Sub-stream - 720P (1280x720), VGA (640x480), QVGA (320x240) Mobile Stream - VGA (640x480), QVGA (320x240)
Max. Frame Rate	20 fps
Video Bitrate	8Kbps - 8Mbps
Network Connection	RJ45 Socket (10/100)
Network Protocols Supported	TCP/IP, HTTP, DHCP, DNS, DDNS, RTP/RTSP, PPPoE, SMTP, NTP, UPnP, SNMP, HTTPS, FTP
Onvif	Yes
Power Over Ethernet (PoE)	Yes
Audio Input	1 Input (RCA), 1 Output (RCA)
Power Input	12V DC Socket (2.1mm)
On Board Recording	Yes - Micro SD Card (Max 256GB)
Alarm Input/Output	Yes
Video Analytics	No
Operating Temperature	-30 to 60°
Dimensions (WHD)	Ø126 x 102.51mm
Weight (kg)	0.96
Warranty	3 Year Warranty

Accessories

Junction Box (Model: JB-003)



Junction Box (Model: JB-005)



Wall Bracket (Model: WB-005)

